

# FMC1322085 DATA SHEET

### SMA Female to SMP Female Cable FM-F086 Coax

### **Electrical Specifications**

Description	Min	Тур	Max	Units				
Frequency Range	DC		10	GHz				
VSWR		1.35:1						
Velocity of Propagation		70.6		%				
Capacitance	28	3.95 [94.9	pF/ft [pF/m]					

# **Mechanical Specifications**

Cable Assembly

Weight 0.0313 lbs [14.2 g]

Cable

Cable Type FM-F086
Impedance 50 Ohms
Inner Conductor Type Solid
Inner Conductor Material and Plating Copper, Si

Dielectric Type

Number of Shields Shield Layer 1 Shield Layer 2 Jacket Material Jacket Diameter Copper, Silver PTFE 2 Silver Plated Copper Tape Silver Plated Copper Braid

FEP, Blue 0.104 in [2.64 mm]

#### **Connectors**

Description	Description Connector 1			
Туре	SMA Female	SMP Female		
Polarity	Standard	Standard		
Impedance	50 Ohms	50 Ohms		
Contact Material & Plating	Beryllium Copper, Gold	Beryllium Copper, Gold		
Contact Plating Spec.	30μ″ Min	30μ in. minimum		
Dielectric Type	PTFE	PTFE		
Body Material & Plating	Gold	Beryllium Copper, Gold		
Body Plating Spec.		30µ in. minimum		

## **Environmental Specifications**

Temperature

Operating Range -65 to +165 deg C

**Compliance Certifications** (see product page for current document)

### **Plotted and Other Data**

Notes:



## **Configuration:**

- SMA Female
- SMP Female
- FM-F086

Fairview Microwave 1130 Junction Dr. #100 Allen, TX 75013


Tel: 1-800-715-4396 / (972) 649-6678

Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





### **Typical Performance Data**



SMA Female to SMP Female Cable FM-F086 Coax from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: SMA Female to SMP Female Cable FM-F086 Coax FMC1322085

URL: https://www.fairviewmicrowave.com/sma-female-smp-female-cable-hs086-coax-fmc1322085-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.


1130 Junction Dr. #100 Allen, TX 75013 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689

Copyright © 2016

REV 1.0 Page 2 of 3







FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM	NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].					
SMA Female to SMP Female Cable FM-F086 Coax	DWG NO FMC1322085			CAGE CODE 3FKR5		
	CAD FILE 103014	SHEET	SCALE	E N/A	SIZE A	5568