



Slide-On BMA Plug Bulkhead to SMA Male Cable FM-SR141TBJ Coax

The BMA plug slide-on bulkhead to SMA male cable using FM-SR141TBJ coax, part number FMCA1619, from Fairview Microwave is in-stock and ships same day. This Fairview BMA to SMA cable assembly has a plug to male gender configuration with 50 ohm formable FM-SR141TBJ coax. Fairview Microwave's formable RF cable assemblies provide an alternative to costly pre-formed semi-rigid assemblies since they are hand formable. The FMCA1619 BMA plug to SMA male cable assembly operates to 18 GHz. Our RF cable assembly with BMA bulkhead interface allows designers to create external connections on their product enclosures, and can be used in a variety of other rack mount and panel mount applications.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Min	Т	ур	Max	ι	Jnits
Frequency Range	DC			18		GHz
VSWR				1.5:1		
Return Loss				15.56		dB
Velocity of Propagation		-	70			%
RF Shielding	100					dB
Group Delay		1.43 [4.69]		ns/ft [ns/m]		
Capacitance		29 [95.14]		pF/f	pF/ft [pF/m]	

Performance by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	1	2	4.5	9	18	GHz
Insertion Loss (Typ.)	0.12	0.16	0.26	0.39	0.58	dB/ft
	0.39	0.52	0.85	1.28	1.9	dB/m

Electrical Specification Notes:

Insertion Loss does not include the loss of the connectors. Insertion Loss is estimated as 0.1 dB per connector.

Mechanical Specifications

Cable Assembly

Diameter 0.315 in [8 mm]

Cable

Cable Type
Impedance
Inner Conductor Type
Inner Conductor Material and Plating
Dielectric Type

FM-SR141TBJ 50 Ohms Solid

Copper Clad Steel, Silver

PTFE







Configuration:

- Slide-On BMA Plug Bulkhead
- SMA Male
- FM-SR141TBJ

Features:

- Max Frequency 18 GHz
- Shielding Effectivity > 100 dB
- 70% Phase Velocity
- FEP Jacket

Applications:

- General Purpose
- · Laboratory Use
- Rack and Panel
- BMA Cable RF Backplanes
- Phased Array Interconnects
- High Speed Switching Networks
- Blind Mate BMA Test

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056

Tel: 1-800-715-4396 / (972) 649-6678

Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





Number of Shields Shield Layer 1 Jacket Material Jacket Diameter

Tinned Copper Braid FEP, Black 0.161 in [4.09 mm]

One Time Minimum Bend Radius Repeated Minimum Bend Radius

0.315 in [8 mm] 1.575 in [40.01 mm]

Connectors

Description	Connector	1 Connector 2			
Туре	BMA Plug	SMA Male			
Mount Method	Bulkhead				
Impedance	50 Ohms	50 Ohms			
Connection Method	Slide-On				
Contact Material & Plating	Bronze, Gold				
Contact Plating Spec.	51.18µ in. minim	num			
Dielectric Type	PTFE				
Outer Cond Material & Plati	ng Brass, Tri-Meta	al			
Outer Cond Plating Spec. 78.74µ in. minimum					
Body Material & Plating	Brass, Tri-Meta	Brass, Gold over Nickel			
Body Plating Spec.	78.74µ in. minimum				
Coupling Nut Material & Plating		Passivated Stainless Steel			
Hex Size	8 mm	5/16 inch			
Torque		8 in-lbs [0.9 Nm]			

Mechanical Specification Notes:

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689

Copyright © 2018


REV 1.1 Page 2 of 5

^{*}All cable assemblies have a length tolerance of 1.5% or \pm 3/8", whichever is greater.





Typical Performance Data



How to Order

Part Number Configuration:

FMCA1619 - xx uu

| cm = Centimeters |
| chlark > = Inches |
| Length

Example: FMCA1619-12 = 12 inches long cable

FMCA1619-100cm = 100 cm long cable





Slide-On BMA Plug Bulkhead to SMA Male Cable FM-SR141TBJ Coax from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.


Click the following link to obtain additional part information: Slide-On BMA Plug Bulkhead to SMA Male Cable FM-SR141TBJ Coax FMCA1619

URL: https://www.fairviewmicrowave.com/bma-plug-sma-male-cable-fm-sr141tbj-coax-fmca1619-p.aspx









STANDARD TOLERANCES ,X ±0.2 ,XX ±0.01 ,XXX ±0.005

*STANDARD TOLERANCES APPLY ONLY TO DIMENSIONS IN INCHES

	FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM	NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].					
	Slide-On BMA Plug Bulkhead to SMA Male Cable FM-SR141TBJ Coax	DWG NO FMCA1619			CAGE CODE 3FKR5		
3K		CAD FILE 12/22/17	SHEET	SCAL	LE N/A SIZE A	CN2245	