

SCB15045-XX

SPECIFICATIONS


CABLE ASSEMBLY:
 VSWR: <1.2 TYPICAL @ 3 GHZ

RAW CABLE: (RG174)
 LOSS (EXCLUDING CONNECTORS)
 @0.1GHz 0.08 DB/FT
 @0.5GHz 0.19 DB/FT
 @1GHz 0.27 DB/FT
 @2GHz 0.39 DB/FT
 @3GHz 0.49 DB/FT


OUTER SHIELD DIAMTER: 0.11"

CONNECTORS:
 SMA: NICKEL PLATED BRASS
 CONTACTS: Au PLATING PER MIL-G-45204
 INTERFACE: MIL-STD-348A

TROQUE WRENCH; 5 IN-IBS



MEASUREMENTS BELOW ARE TYPICAL



ALL DIMENSIONS IN inches(MM) Typical

FAIRVIEW MICROWAVE INC.			
ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM			
TITLE			
SMA FLEXABLE CABLES 3GHZ RG 174			
SIZE	CAGE CODE	DWG NO	REV
A	3FKR5	SCB15045-XX	A
SCALE		SHEET	