

# SCB15052-XX

## SPECIFICATIONS


CABLE ASSEMBLY:  
 VSWR: <1.2 dB TYPICAL @ 6GHZ

RAW CABLE:  
 LOSS (EXCLUDING CONNECTORS)  
 @ 1GHZ: 0.08 DB/FT  
 @ 2GHZ: 0.16 DB/FT  
 @ 3GHZ: 0.11 DB/FT


OUTER DIAMETER: 0.195"

CONNECTORS:  
 SMA: NICKEL PLATED BRASS  
 CONTACTS: Au PLATING  
 INTERFACE: MIL-STD-348A

TORQUE WRENCH; 5 IN-IBS



### MEASUREMENTS BELOW ARE TYPICAL



ALL DIMENSIONS IN inches(MM) Typical

<b>FAIRVIEW MICROWAVE INC.</b>			
ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM			
TITLE			
<b>SMA FLEXABLE CABLES 6GHZ LMR200</b>			
SIZE	CAGE CODE	DWG NO	REV
<b>A</b>	3FKR5	<b>SCB15052-XX</b>	--
SCALE		SHEET	