

SCB15070-XX

SPECIFICATIONS


CABLE ASSEMBLY:
 VSWR: <1.2 TYPICAL @ 6 GHZ

RAW CABLE:
 LOSS (EXCLUDING CONNECTORS)
 @ 1GHZ: 0.13 DB/FT
 @ 2GHZ: 0.20 DB/FT
 @ 3GHZ: 0.25 DB/FT


OUTER ID: 0.212

CONNECTORS:
 SMA: NICKEL PLATED BRASS
 CONTACTS: Au PLATING
 INTERFACE: MIL-STD-348A

TROQUE WRENCH; 5 IN-IBS



MEASUREMENTS BELOW ARE TYPICAL



ALL DIMENSIONS IN inches(MM) Typical

FAIRVIEW MICROWAVE INC.

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE

SMA FLEXIBLE CABLES 6 GHZ RG223

SIZE	CAGE CODE	DWG NO	REV
A	3FKR5	SCB15070-XX	A
SCALE	SHEET		