

SMA FLEXIBLE CABLES 3 GHZ RG58CU

SCB15173-XX

SPECIFICATIONS

CABLE ASSEMBLY:

VSWR: <1.2 dB TYPICAL @ 3 GHZ

RAW CABLE:

LOSS (EXCLUDING CONNECTORS)

@ 1GHZ: 0.21 DB/FT

@ 2GHZ: 0.36 DB/FT

@ 3GHZ: 0.49 DB/FT

OUTER DIAMETER: 0.195"


CONNECTORS:

SMA: NICKEL PLATED BRASS


CONTACTS: Au PLATING PER

INTERFACE: MIL-STD-348A

TORQUE WRENCH: 5 IN-IBS



MEASUREMENTS BELOW ARE TYPICAL



ALL DIMENSIONS IN inches(MM) Typical

FAIRVIEW MICROWAVE INC.			
ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM			
TITLE			
SMA FLEXIBLE CABLES 3 GHZ RG58CU			
SIZE	CAGE CODE	DWG NO	REV
A	3FKR5	SCB15173-XX	--
SCALE		SHEET	