

# SCB15780-XX

## SPECIFICATIONS


CABLE ASSEMBLY:  
 VSWR: <1.2 TYPICAL @ 3 GHZ

RAW CABLE: (RG316DS)  
 LOSS (EXCLUDING CONNECTORS)  
 @ 1GHZ: 0.30 DB/FT  
 @ 2GHZ: 0.45 DB/FT  
 @ 3GHZ: 0.57 DB/FT


OVERALL DIAMETER: 0.11"

CONNECTORS:  
 SMA: NICKEL PLATED BRASS  
 CONTACTS: Au PLATING  
 INTERFACE: MIL-STD-348A

TORQUE WRENCH: 5 IN-IBS



### MEASUREMENTS BELOW ARE TYPICAL



ALL DIMENSIONS IN inches(MM) Typical

## FAIRVIEW MICROWAVE INC.

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE

SMA FLEXABLE CABLES RG316DS 3GHZ

SIZE	CAGE CODE	DWG NO	REV
A	3FKR5	SCB15780-XX	A
SCALE	SHEET		