

WR-10 Directional Waveguide Coupler 10 dB With UG 387/U-Mod Flange and H-Plane Coupled Port From 75 GHz to 110 GHz W Band

The SMW10HC001-10 is a millimeter-wave directional waveguide coupler that operates in the frequency range of 75 to 110 GHz (W Band). This W band component offers a nominal coupling level of 10 dB, mean coupling accuracy of ± 1 , coupling flatness of 1.5 dB, and has a maximum VSWR level of 1.2:1. The design is made of gold plated brass copper and incorporates a multi-hole configuration that results in typical directivity of 30 dB. Common applications for this millimeter wave component involve test setups where power reflection measurements are required that might involve power sampling and frequency monitoring with minimal signal loss to the main transmission path. This H plane coupler uses integrated WR-10 waveguide ports with UG 387/U-Mod flanges. Fairview offers a complete family of waveguide millimeter wave directional couplers that are in-stock for same day shipment.

Electrical Specifications*

Description	Min	Typ	Max	Units
Frequency Range	75		110	GHz
Directivity		30		dB
Insertion Loss			1.4	dB
Input VSWR			1.2:1	
Secondary Line VSWR			1.2:1	
Nominal Coupling Level		10		dB
Mean Coupling Accuracy			± 1	dB
Coupling Flatness			± 1.5	dB

* Values at 25°C, sea level

Mechanical Specifications

Size

Length	3.5 in [88.9 mm]
Width/Dia.	1 in [25.4 mm]
Height	0.82 in [20.83 mm]

Waveguide

Size	WR-10
Material	Brass Copper
Plating	Gold
Color	Gold

Flange 1

Interface	UG 387/U-Mod
Material	Brass Copper
Plating	Gold
Color	Gold

Flange 2

Interface	UG 387/U-Mod
Material	Brass Copper
Plating	Gold
Color	Gold



Features:

- 10 dB Nominal Coupling Level
- H-Plane Waveguide Coupler
- 75 GHz to 110 GHz Frequency Range
- Body and Flanges made of Brass Copper
- Gold Plated Waveguide
- 1.2:1 VSWR

Fairview Microwave
1130 Junction Dr. #100
Allen, TX 75013
Tel: 1-800-715-4396 / (972) 649-6678
Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com

Flange 3

Interface	UG 387/U-Mod
Material	Brass Copper
Plating	Gold
Color	Gold

Compliance Certifications (visit www.FairviewMicrowave.com for current document)

RoHS Compliant	Yes
----------------	-----

Plotted and Other Data

Notes:


- Values at 25 °C, sea level

WR-10 Directional Waveguide Coupler 10 dB With UG 387/U-Mod Flange and H-Plane Coupled Port From 75 GHz to 110 GHz W Band from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [WR-10 Directional Waveguide Coupler 10 dB With UG 387/U-Mod Flange and H-Plane Coupled Port From 75 GHz to 110 GHz W Band SMW10HC001-10](http://www.fairviewmicrowave.com/wr-10-directional-waveguide-coupler-10db-ug-387-mod-h-plane-smw10hc001-10-p.aspx)

URL: <http://www.fairviewmicrowave.com/wr-10-directional-waveguide-coupler-10db-ug-387-mod-h-plane-smw10hc001-10-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.



UNLESS OTHERWISE SPECIFIED:

DIMENSIONS ARE IN: inches
TOLERANCES ARE: [mm]
.XX ± .02 [±.51]
.XX ± .005 [±.13]

* THESE DIMENSIONS AND TOLERANCES
SUPERSEDE NOTE #1 ON TITLE BLOCK.

FAIRVIEW MICROWAVE INC.
ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

NOTES:
1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
3. DIMENSIONS ARE IN INCHES [mm].

TITLE
WR-10 Directional Waveguide Coupler 10 dB With UG 387/U-Mod Flange and H-Plane Coupled Port From 75 GHz to 110 GHz W Band

DWG NO	SMW10HC001-10		CAGE CODE	3FKR5	
CAD FILE	063015	SHEET	SCALE	N/A	SIZE A 2233