

COUPLER N-F's 4-8 GHZ

MC4052


SPECIFICATIONS

ELECTRICAL

FREQUENCY: 4-8 GHZ
 DIRECTIVITY: 17 DB MIN
 IMPEDANCE: 50 OHMS
 VSWR: 1.5:1 MAX , ALL PORTS
 FLATNESS: +/- 1.25 DB
 LOSS, THRU LINE: .35DB

MATERIALS

BODY: PASSIVATED ALUMINUM
 CONNECTORS: N-FEMALE, NICKLE PLATING
 CONNECTOR CONTACTS: BeCu, Au PLATING
 CONNECTOR DIELECTRIC: TEFLON
 CONNECTOR INTERFACE: MIL-STD-348A
 PAINT: BLUE



				FAIRVIEW MICROWAVE INC.	
				ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM	
				TITLE	
				COUPLER N-F's 4-8 GHZ	
		SIZE	CAGE CODE	DWG NO	REV
		A	3FKR5	MC4052	
				SCALE	SHEET