

COUPLER N-F's 7-12.4 GHZ

MC4067


SPECIFICATIONS

ELECTRICAL

FREQUENCY: 7-12.4 GHZ
 DIRECTIVITY: 15 DB MIN
 IMPEDANCE: 50 OHMS
 VSWR: 1.5:1 MAX , ALL PORTS
 FLATNESS: +/- 1.25 DB
 LOSS, THRU LINE: .4 DB

MATERIALS

BODY: PASSIVATED ALUMINUM
 CONNECTORS: N-FEMALE, NICKLE PLATING
 CONNECTOR CONTACTS: BeCu, Au PLATING
 CONNECTOR DIELECTRIC: TEFLON
 CONNECTOR INTERFACE: MIL-STD-348A
 PAINT: BLUE



FAIRVIEW MICROWAVE INC.

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE

COUPLER N-F's 7-12.4 GHZ

SIZE	CAGE CODE	DWG NO	REV
A	3FKR5	MC4067	
SCALE	SHEET		