

SMA POWER DIVIDER 2-WAY 0.8-2.4 GHZ

MP8305

SPECIFICATIONS

ELECTRICAL:

FREQUENCY: 0.8-2.4 GHZ
 VSWR 1.3:1 MAX IN, 1.20 OUT
 POWER CW: 20 WATTS INTO 1.2:1 VSWR;
 10 WATTS INTO 2:1 VSWR;
 3 WATT INTO OPEN


ISOLATION: 22 DB MIN
 INSERTION LOSS: 3.4 DB (3+.4)
 AMPLITUDE BALANCE: +/- 0.2DB MAX
 PHASE BALANCE: 3 DEGREES MAX
 IMPEDANCE: 50 OHMS

MECHANICAL

CONNECTORS: NICKEL PLATED BRASS
 CONTACTS: GOLD PLATED

ENVIRONMENTAL:

TEMP: -55 C TO +125 C



				FAIRVIEW MICROWAVE INC.	
				ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM	
				TITLE	
				SMA POWER DIVIDER 2-WAY 0.8-2.4 GHZ	
SIZE	CAGE CODE	DWG NO			REV
A	3FKR5		MP8305		
SCALE					SHEET