

POWER DIVIDER N 10-14 GHZ

MP8794


SPECIFICATIONS

ELECTRICAL

FREQUENCY: 10-14 GHZ
ISOLATION: 15 DB MIN
POWER: 30 W AVG INTO 1.2:1 VSWR
IMPEDANCE: 50 OHMS
VSWR: 1.65:1 MAX i/o
LOSS: 3.7 DB MAX (3+.7)

MECHANICAL

MATERIALS BODY: PASSIVATED ALUMINUM
CONNECTORS: N-FEMALE, NICKEL PLATING
CONNECTOR CONTACTS: BeCu, Au PLATING
CONNECTOR DIELECTRIC: TEFLON
CONNECTOR INTERFACE: MIL-STD-348A
PAINT: BLUE



FAIRVIEW MICROWAVE INC.

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE

POWER DIVIDER N 10-14 GHZ

SIZE	CAGE CODE	DWG NO	REV
A	3FKR5	MP8794	

SCALE

SHEET