

2.92 POWER DIVIDER RESISTIVE 2WAY 40 GHZ

MPR40-2


SPECIFICATIONS

ELECTRICAL:

RESISTIVE POWER DIVIDER
 FREQUENCY: 0-40 GHZ
 VSWR 1.7:1 MAX
 POWER: 1 WATT CW, 1KW PEAK
 5 μSEC PULSE WIDTH, 0.05% DUTY CYCLE, INPUT ONLY)
 INSERTION LOSS: 10.5 DB MAX(BETWEEN INPUT & EITHER OUTPUT)
 IMPEDANCE: 50 OHMS

MATERIALS BODY: BRASS
 CONNECTORS: STAINLESS STEEL
 CONTACTS BeCU, Au PLATING MIL-G-45204
 BODY: NICKEL PLATED BRASS

TEMP: -55° TO +125° C



				FAIRVIEW MICROWAVE INC.			
				ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM			
				TITLE			
				2.92 POWER DIVIDER RESISTIVE 2WAY 40 GHZ			
SIZE	CAGE CODE	DWG NO				REV	
A	3FKR5	MPR40-2					
SCALE				SHEET			