

# BNC ATTENUATORS

SA01B-XX

## SPECIFICATIONS


### ELECTRICAL

FREQUENCY: 0-1 GHZ  
IMPEDANCE: 50 OHMS  
VSWR: 1.15:1 MAX  
POWER: 0.5 WATTS CW @ 25 DEG C

### MECHANICAL

MATERIALS BODY : BRASS PER QQ-B-626  
PLATING: TR-METAL (TIN-ZINC-COPPER)  
CONTACT PLATING: Au

ROHS COMPLIANT



				<b>FAIRVIEW MICROWAVE INC.</b>			
				ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM			
				TITLE			
				<b>BNC ATTENUATORS</b>			
SIZE		CAGE CODE		DWG NO		REV	
<b>A</b>		3FKR5		SA01B-XX		<b>A</b>	
SCALE						SHEET	