

SMA-M CONN .141SR DIRECT SOLDER

SC3010

SPECIFICATIONS

ELECTRICAL:


FREQUENCY: 0-18 GHZ
 VSWR 1.3:1 MAX
 IMPEDANCE: 50 OHMS
 OP. TEMP RANGE: -55C- +155C

MECHANICAL:

MATERIAL BODY: STAINLESS STEEL AU PLATING 3μ"
 CENTER CONTACT: BRASS
 CONTACT PLATING: Au PER MIL-G-45204
 ROHS COMPLIANT

ASSEMBLY

TRIM CABLE AS SHOWN,
 SOLDER PIN TO CENTER CONDUCTOR,
 INSERT CABLE INTO SMA BODY,
 SOLDER CABLE JACKET WHILE KEEPING END OF
 CABLE FLUSH WITH TEFLON & CHECKING FINAL
 PIN DEPTH



FAIRVIEW MICROWAVE INC.

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE

SMA-M CONN .141SR DIRECT SOLDER

SIZE	CAGE CODE	DWG NO	REV
A	3FKR5	SC3010	--
SCALE	SHEET		