

SPECIFICATIONS

CABLE ASSEMBLY:


VSWR: 1.25:1 TYPICAL @ 18GHZ
 VSWR 1.40:1 MAX @ 18GHZ

RAW CABLE: (HAVERHILL HFLEX .086 OR EQ)
 LOSS (EXCLUDING CONNECTORS)
 @ 1GHZ: 0.23 DB/FT
 @10GHZ: 0.8 DB/FT
 @18GHZ: 1.1 DB/FT

OUTER SHIELD DIAMETER: .086"
 OVERALL DIAMETER: .104"

CONNECTORS:

SMA: NICKEL PLATED BRASS
 CONTACTS: Au PLATING PER MIL-G-45204
 INTERFACE: MIL-STD-348A



				FAIRVIEW MICROWAVE INC.	
				ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM	
				TITLE	
				SMA FLEXIBLE CABLES 18GHZ 0.086"	
SIZE		CAGE CODE	DWG NO	REV	
A		3FKR5	SCA52086-XX	--	
SCALE			SHEET		