

SMA FLEXABLE CABLES 18GHZ 0.141"

SCA52141-XX

SPECIFICATIONS

CABLE ASSEMBLY:

VSWR: 1.20:1 TYPICAL @ 18GHZ
 VSWR 1.30:1 MAX @ 18GHZ


RAW CABLE: (HAVERHILL HFLEX .141 OR EQ)

TYPICAL LOSS (EXCLUDING CONNECTORS)
 @ 1GHZ: 0.13 DB/FT
 @ 10GHZ: 0.45 DB/FT
 @ 18GHZ: 0.64 DB/FT

OUTER SHIELD DIAMETER: .141"
 OVERALL DIAMETER: .163"

CONNECTORS:

SMA: NICKEL PLATED BRASS
 CONTACTS Au PLATING PER MIL-G-45204
 INTERFACE: MIL-STD-348A



				FAIRVIEW MICROWAVE INC.			
				ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM			
				TITLE			
				SMA FLEXABLE CABLES 18GHZ 0.141"			
SIZE		CAGE CODE		DWG NO		REV	
A		3FKR5		SCA52141-XX		A	
SCALE				SHEET			