

# SMA/M TO MMCX JACK ADAPTER

SM4781

## SPECIFICATIONS

### ELECTRICAL

50 OHMS  
VSWR 1.25:1 MAX  
FREQUENCY: DC-6 GHZ

### MECHANICAL

100 CYCLES MIN  
3-5 IN-LBS COUPLING NUT MATING TORQUE


### ENVIRONMENTAL

-55 DEG C TO +155 DEG C  
INTERFACE: MIL-STD-348

### MATERIALS

BODY: Au PLATED BRASS  
CENTER CONTACT: BeCu  
CONTACT PLATING: Au PER MIL-G-45204  
INSULATION: TEFLON

ROHS COMPLIANT



**FAIRVIEW MICROWAVE INC.**

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE

**SMA/M TO MMCX JACK ADAPTER**

SIZE	CAGE CODE	DWG NO	REV
<b>A</b>	<b>3FKR5</b>	<b>SM4781</b>	--

SCALE

SHEET