

1.0/2.3 - SMA ADAPTERS


SM5525, SM5530, SM5535, SM5540


SPECIFICATIONS

ELECTRICAL
 50 OHMS
 FREQUENCY: 0-6 GHZ
 VSWR 1.15:1 MAX @ 6 GHZ

BODY: BRASS, Au PLATING
 FEMALE CONTACTS: BeCu
 MALE CONTACTS: BRASS
 CONTACT PLATING: Au PER MIL-G-45204
 NUT: BRASS, TRIMETAL PLATING
 TEMPERATURE -40 TO +120° C


RoHS COMPLIANT

1.0/2.3 JACK  SMA JACK





SM5525

1.0/2.3 JACK  SMA PLUG




SM5530

1.0/2.3 PLUG  SMA JACK



SM5535

1.0/2.3 PLUG  SMA PLUG



SM5540

FAIRVIEW MICROWAVE INC.

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE

1.0/2.3 - SMA ADAPTERS

SIZE	CAGE CODE	DWG NO	REV
A	3FKR5	SM5525, SM5530, SM5535, SM5540	--

SCALE	SHEET
-------	-------