

# N/F-TNC/M/REV POLARITY ADAPTER

SM5795

## SPECIFICATIONS


### ELECTRICAL

FREQUENCY: 0-6 GHZ  
IMPEDANCE: 50 OHMS  
VSWR: 1.3:1 MAX 6GHZ

### MECHANICAL

MATERIALS BODY NICKLE PLATED BRASS  
MATERIALS CONTACTS BeCu Au PLATING MIL-G-45204  
INSULATOR: TEFLON  
DURABILITY: 500 CYCLES MIN  
TEMPERATURE RANGE: -45 TO +120°C

TNC-M-RP  
SOCKET, NO PIN



N-F

1.49"

**FAIRVIEW MICROWAVE INC.**

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE

**N/F-TNC/M/REV POLARITY ADAPTER**

SIZE

**A**

CAGE CODE

3FKR5

DWG NO

**SM5795**

REV

**B**

SCALE

SHEET