



# SMA F'S 60° PHASESHIFTERS DC-2.3 GHZ

SMP0223

2X  
4-40 X .25 DP  
MOUNTING HOLE



4X  
4-40 MOUNTING  
HOLE

4X Ø0.12" THRU HOLE

0.36"

.38"


1.00"

## SPECIFICATIONS

### ELECTRICAL:

- FREQUENCY: DC-2.3 GHZ
- VSWR 1.5:1 MAX
- POWER CW: 100 WATTS
- POWER PEAK: 3KW
- IMPEDANCE: 50 OHMS
- INSERTION LOSS: 0.5 DB MAX
- MIN. ADJUSTABLE PHASE SHIFT: 0 TO 60°/GHZ
- INSERTION PHASE @ 1 GHZ: 320°(MIN SETTING)

MATERIAL CONNECTORS: STAINLESS STEEL  
MATERIAL BODY: ALUMINUM



5.50"

**FAIRVIEW MICROWAVE INC.**

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE

**SMA F'S 60° PHASESHIFTERS  
DC-2.3 GHZ**

SIZE	CAGE CODE	DWG NO	REV
<b>A</b>	<b>3FKR5</b>	<b>SMP0223</b>	--
SCALE		SHEET	