



DETAIL A

HYBRID, D-SUB 7-PIN MALE		
PIN #	DESCRIPTION	SPECIFICATIONS
A1	VDD	28 VDC
A2	GND	Ground
1	ENABLE	Amplifier Enable: TTL Logic High (3.3V) (Internally Pulled-Low)
2	CURRENT SENSE	Analog voltage relative to IDD@ 100mV per Ampere
3	TEMP SENSE	Analog voltage relative to Module's Temperature @ 10 mV/°C
4	NC	No electrical connection
5	GND	Ground

LABEL

Fairview Microwave

an INFINITI® brand


FMAM5063

S/N: XXXXXXX

STANDARD TOLERANCES	
.X	±0.2
.XX	±0.01
.XXX	±0.005

*STANDARD TOLERANCES APPLY ONLY TO DIMENSIONS IN INCHES

- NOTES:
- ADEQUATE HEATSINK REQUIRED.



Fairview Microwave

an INFINITI® brand

NOTES:
1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
3. DIMENSIONS ARE IN INCHES [mm].

TITLE		DWG NO		CAGE CODE	
		FMAM5063		3FKR5	
CAD FILE	07/30/19	SHEET	1 OF 1	SCALE	N/A
				SIZE	A
				7361	