





HYBRID, D-SUB 7-PIN MALE			
PIN #	DESCRIPTION	SPECIFICATIONS	
A1	VDD	28 VDC	
A2	GND	Ground	
1	ENABLE	Amplifier Enable: TTL Logic High (3.3V) (Internally Pulled-Low)	
2	TEMP SENSE	Analog voltage relative to Module's Temperature @ 10 mV/°C	
3	CURRENT SENSE	Analog voltage relative to ID/D@ 100mV per Ampere	
4	NC	No electrical connection	
5	GND	Ground	

Fairview Microwave
an INFINITO® brand
FMAM5071
S/N: XXXXXX

STANDARD TOLERANCES

.X	±0.2
.XX	±0.01
.XXX	±0.005

Fairview Microwave
an INFINIT@ brand

NOTES:

1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
3. DIMENSIONS ARE IN INCHES [mm].

DWG NO	CAGE CODE
FMAM5071	3FKR5

7361