



UNLESS OTHERWISE SPECIFIED
LEADING DIMENSIONS ARE INCHES
DIMENSIONS IN [] ARE MILLIMETERS

TOLERANCES:

	FRACTIONS
X = ±.2 [5]	± 1/32
XX = ±.02 [0.5]	± .001
XXX = ±.005 [0.13]	± .0005

ANGLES ± 1°

CABLE LENGTH TOLERANCES:

Length (in)	Length (mm)	Tolerance (in)	Tolerance (mm)
≤ 12	≤ 305	± .1	± 2.5
> 12	305 ≤ 60	± .15	± 3.8
> 60	1524 ≤ 120	± .2	± 5.1
> 120	3048 ≤ 300	± .3	± 7.6
> 300	7620	± .5	± 12.7

ALL DIMENSIONS ARE FOR REFERENCE ONLY
AND SUBJECT TO CHANGE WITHOUT NOTICE
UN-DIMENSIONED NON-CRITICAL FEATURES
MAY VARY IN SIZE AND LOCATION
COLORS MAY VARY

Fairview Microwave®
an INFINIT® brand

Website: www.FairviewMicrowave.com
Phone: 1.800.715.4396 | 1.972.649.6678

INTERPRET ALL DIMENSIONS AND
TOLERANCES PER ASME Y14.5

SCALE: NONE
SHEET: 1 OF 1

DESCRIPTION

WiFi 6, 2400-2500/5150-5850 MHz 6/6 dBi, 8x8 MIMO PANEL, N-MALE

SIZE	CAGE CODE	DRAWN BY	ITEM NO.	REV
A	3FKR5	HBAKKE	FMANFP1075	A