




|           |                    |
|-----------|--------------------|
| TOLERANCE | .XX ± .02 [.50]    |
| IN [mm]   | .XXX ± .005 [.127] |
| ANG.      | ± 1/2°             |

\* THESE DIMENSIONS AND TOLERANCES  
SUPERSEDE NOTE #1 ON TITLE BLOCK.

| PORT CONFIGURATION |             |             |             |             |
|--------------------|-------------|-------------|-------------|-------------|
| INPUT              | J1          | J2          | J3          | J4          |
| J1                 | ---         | ISOLATION   | -3dB<0 DEG  | -3dB<90 DEG |
| J2                 | ISOLATION   | ---         | -3dB<90 DEG | -3dB<0 DEG  |
| J3                 | -3dB<0 DEG  | -3dB<90 DEG | ---         | ISOLATION   |
| J4                 | -3dB<90 DEG | -3dB<0 DEG  | ISOLATION   | ---         |

# FAIRVIEW MICROWAVE INC.

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

NOTES:  
1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.  
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.  
3. DIMENSIONS ARE IN INCHES [mm].

|          |        |          |  |           |      |
|----------|--------|----------|--|-----------|------|
| TITLE    |        | DWG NO   |  | CAGE CODE |      |
|          |        | FMCP1033 |  | 3FKR5     |      |
| CAD FILE | 121415 | SHEET    |  | SCALE     | N/A  |
|          |        |          |  | SIZE      | A    |
|          |        |          |  |           | 2233 |