



.030 [.76] MAX. EYELET PROJ.
.120 [3.05] MAX. EYELET DIA.
(TYP. EACH SIDE, SMALL EYELETS)



.030 [.76] MAX. EYELET PROJ.
.220 [5.59] MAX. EYELET DIA.
(TYP. EACH SIDE, LARGE EYELETS)

TOLERANCE	.XX ± .02 [.50]
IN [mm]	.XXX ± .005 [.127]
ANG.	± 1/2°

* THESE DIMENSIONS AND TOLERANCES
SUPERSEDE NOTE #1 ON TITLE BLOCK.

PORT CONFIGURATION				
INPUT	J1	J2	J3	J4
J1	---	ISOLATION	-3dB<0 DEG	-3dB<90 DEG
J2	ISOLATION	---	-3dB<90 DEG	-3dB<0 DEG
J3	-3dB<0 DEG	-3dB<90 DEG	---	ISOLATION
J4	-3dB<90 DEG	-3dB<0 DEG	ISOLATION	---

FAIRVIEW MICROWAVE INC.

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

NOTES:
1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
3. DIMENSIONS ARE IN INCHES [mm].

TITLE	DWG NO		CAGE CODE	
	FMCP1041		3FKR5	
CAD FILE	042116	SHEET	SCALE N/A	SIZE A
				2233