





REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	PCR FMSW6140 2019129	12/10/19	T.GALLA



Label	Function
4	TTL Port 4
3	TTL Port 3
2	TTL Port 2
1	TTL Port 1
+A	+12 Vdc
-B	- Return

Label	Function
1	Indicator Port 1
2	Indicator Port 2
3	Indicator Port 3
4	Indicator Port 4
COM	Indicator Common

* Indicator Contacts Rating: 250mA, 100Vdc, 5W max (switching); Must use a series current limiting resistor.



CAUTION
STATIC SENSITIVE

www.pasternack.com
 MODEL NO.: FMSW6140
 VOLTAGE : 12 VDC
 V0001188MMDDYYYYXXXXX

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS, DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

Fairview Microwave
 an INFINITT® brand



UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES
 DIMENSIONS IN [] ARE MILLIMETERS
 TOLERANCES:
 CABLE LENGTH (L) TOLERANCES:
 L ± 1/2 (806) = +1/2 (25) / -0
 12 (305) < L ≤ 60 (1524) = +2 (51) / -0
 60 (1524) < L ≤ 120 (3048) = +4 (102) / -0
 120 (3048) < L ≤ 300 (7620) = +6 (152) / -0
 300 (7620) < L = +5%L / -0
 THE INFORMATION AND DESIGN IN THIS DOCUMENT IS THE PROPERTY OF FAIRVIEW MICROWAVE CORPORATION. ALL RIGHTS RESERVED.

SIZE	GAGE CODE	DRAWN BY	PART NUMBER	SCALE	REV
A	3FKR5	K.DANG	FMSW6140	N/A	A