





7X "K" CONN FEM  
6 PLCS ON Ø1.062 B.C.  
(2.92mm)



UNLESS OTHERWISE SPECIFIED  
DIMENSIONS ARE IN INCHES.  
TOLERANCES ARE:

DECIMALS ANGLES FRACTIONS  
.XX ± .03 ± 1° ± 1/16  
.XXX ± .010

| HOLE DIAMETER  | TOLERANCE    |
|----------------|--------------|
| .0135 TO .125  | +.004/- .001 |
| .126 TO .250   | +.005/- .001 |
| .251 TO .500   | +.006/- .001 |
| .501 TO .750   | +.008/- .001 |
| .751 TO 1.000  | +.010/- .001 |
| 1.001 TO 2.000 | +.012/- .001 |

\* THESE DIMENSIONS AND TOLERANCES  
SUPERSEDE NOTE #1 ON TITLE BLOCK.

**FAIRVIEW MICROWAVE INC.**  
ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

NOTES:  
1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.  
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.  
3. DIMENSIONS ARE IN INCHES [mm].

TITLE

DWG NO

FMSW6147

CAGE CODE

3FKR5

CAD FILE 031915

SHEET

SCALE N/A

SIZE A

200