



UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. TOLERANCES ARE:		ANGLES ±1° FRACTIONS ±1/16	
DECIMALS .XX ± .03 (0.76) .XXX ± .010 (0.254)			
HOLE DIAMETER .0135 TO .125 (0.343 TO 3.175)	TOLERANCE + .004 TO -.001 (+.0102 TO -.0025)		
.126 TO .250 (3.200 TO 6.350)	+ .005 TO -.001 (+.0127 TO -.0025)		
.251 TO .500 (6.375 TO 12.700)	+ .006 TO -.001 (+.0152 TO -.0025)		
.501 TO .750 (12.725 TO 19.050)	+ .008 TO -.001 (+.0203 TO -.0025)		
.751 TO 1.000 (19.075 TO 25.400)	+ .010 TO -.001 (+.0254 TO -.0025)		
1.001 TO 2.000 (25.425 TO 50.800)	+ .012 TO -.001 (+.0305 TO -.0025)		

\* THESE DIMENSIONS AND TOLERANCES  
SUPERSEDE NOTE #1 ON TITLE BLOCK.

**FAIRVIEW MICROWAVE INC.**  
ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

NOTES:  
1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.  
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.  
3. DIMENSIONS ARE IN INCHES [mm].

TITLE		DWG NO		CAGE CODE	
		FMSW6201		3FKR5	
CAD FILE	062915	SHEET		SCALE	N/A
		SIZE	A		2233