





PWR



UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. TOLERANCES ARE:	
DECIMALS .XX ± .03 (0.76) .XXX ± .010 (0.254)	ANGLES ±1° FRACTIONS ±1/16
HOLE DIAMETER Ø.343 TO .125 (0.343 TO 3.175)	TOLERANCE + .004 TO - .001 (+0.102 TO -0.025)
.126 TO .250 (3.200 TO 6.350)	+ .005 TO - .001 (+0.127 TO -0.025)
.251 TO .500 (6.375 TO 12.700)	+ .006 TO - .001 (+0.152 TO -0.025)
.501 TO .750 (12.725 TO 19.050)	+ .008 TO - .001 (+0.203 TO -0.025)
.751 TO 1.000 (19.075 TO 25.400)	+ .010 TO - .001 (+0.254 TO -0.025)
1.001 TO 2.000 (25.425 TO 50.800)	+ .012 TO - .001 (+0.305 TO -0.025)

* THESE DIMENSIONS AND TOLERANCES
SUPERSEDE NOTE #1 ON TITLE BLOCK.

FAIRVIEW MICROWAVE INC.

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

NOTES:
1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
3. DIMENSIONS ARE IN INCHES [mm].

TITLE		DWG NO		CAGE CODE	
		FMSW6203		3FKR5	
CAD FILE	062915	SHEET		SCALE	N/A
				SIZE	A
					2233