





REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	03-01-2021	TGALLA



- NOTES:
- LABEL PER ILS-100-05. FOR INTERNAL REFERENCE ONLY.
LABEL LOCATION SHOULD BE SAME AS SHOWN.
 - SERIAL NUMBER AND DATE CODE ARE COMBINED. EX: 202008280001.

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS, DIVERSION CONTRARY TO U.S. LAW PROHIBITED.



UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [] ARE MILLIMETERS					THIRD-ANGLE PROJECTION	
TOLERANCES:						
CABLE LENGTH (L) TOLERANCES:						
X = ±.2	[5.08]	FRACTIONS	12 [305] < L ≤ 60 [1524] = +2 [51] / -0			
XX = ±.02	[.51]	± 1/32	60 [1524] < L ≤ 120 [3048] = +4 [102] / -0			
XXX = ±.005	[.13]	ANGLES ± 1°	120 [3048] < L ≤ 300 [7620] = +6 [152] / -0			
			300 [7620] < L = +5%L / -0			
ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY.				SCALE	N/A	
SIZE	CAGE CODE	DRAWN BY	ITEM NO.			
A	3FKR5	MVEERAPPAN	FMWC31019	REV	A	