





REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	PCR SA4N25-XX	12/21/2020	S.FONG



THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS, DIVERSION CONTRARY TO U.S. LAW PROHIBITED.



TITLE

UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [] ARE MILLIMETERS			
TOLERANCES:		CABLE LENGTH (L) TOLERANCES:	
X = ±.2 [5.08]	FRACTIONS XX = ±.02 [.51]	L ± 1/2 (B06) = +1 [25] / -0	THIRD-ANGLE PROJECTION
XXX = ±.005 [.13]	ANGLES ± 1°	12 [305] < L ≤ 60 [1524] = +2 [51] / -0	THE INFORMATION AND DESIGN IN THIS DOCUMENT IS THE PROPERTY OF FAIRVIEW MICROWAVE CORPORATION. ALL RIGHTS RESERVED.
ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY.		60 [1524] < L ≤ 120 [3048] = +4 [102] / -0	120 [3048] < L ≤ 300 [7620] = +6 [152] / -0
SIZE	GAGE CODE	DRAWN BY	ITEM NO.
A	3FKRS	K.DANG	SA4N25-30
SCALE			REV
N/A			A