

## Bend Relief TRB Plug to Blunt Cut Genderless 1553 Cable 36 Inch Length Using 78 Ohm M17/176-00002 Coax

The 78 ohm TRB 3-Slot plug to Blunt cut genderless 36 inch cable using 78 ohm M17/176-00002 twinax, part number FM3CA2342-36, from Fairview Microwave is in-stock and ships same day. This Fairview TRB 3-Slot to Blunt Cut cable assembly has a plug to genderless gender configuration with 78 ohm flexible M17/176-00002 twinax. Fairview Microwave's flexible RF cable assemblies are ideal for applications where tight bends and continual flexure are required. The FM3CA2342-36 TRB 3-Slot plug to Blunt cut genderless cable assembly operates to 10 MHz.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

### Electrical Specifications

| Description            | Min | Typ        | Max     | Units        |
|------------------------|-----|------------|---------|--------------|
| Frequency Range        | DC  |            | 10      | MHz          |
| Capacitance            |     | 24 [78.74] |         | pF/ft [pF/m] |
| Operating Voltage (AC) |     |            | 750,000 | Vrms         |

### Mechanical Specifications

#### Cable Assembly

|         |                     |
|---------|---------------------|
| Length* | 36 in [914.4 mm]    |
| Weight  | 0.104 lbs [47.17 g] |

#### Cable

|                                      |                      |
|--------------------------------------|----------------------|
| Cable Type                           | M17/176-00002        |
| Impedance                            | 78 Ohms              |
| Inner Conductor Type                 | Stranded             |
| Inner Conductor Material and Plating | Copper, Silver       |
| Dielectric Type                      | PTFE                 |
| Shield Layer 1                       | Silver Plated Copper |
| Jacket Material                      | PFA, Blue            |

|                              |                  |
|------------------------------|------------------|
| One Time Minimum Bend Radius | 1.5 in [38.1 mm] |
|------------------------------|------------------|



### Configuration:

- TRB 3-Slot Plug
- Blunt Cut Genderless
- M17/176-00002

### Features:

- Max Frequency 10 MHz
- PFA Jacket
- MIL-STD-1553
- -55°C to +200°C
- 78 ohms

### Applications:

- General Purpose
- Laboratory Use
- Vehicle High Temperature
- Data
- MIL-STD-1553

Fairview Microwave  
 301 Leora Ln., Suite 100  
 Lewisville, TX 75056  
 Tel: 1-800-715-4396 / (972) 649-6678  
 Fax: (972) 649-6689  
[www.fairviewmicrowave.com](http://www.fairviewmicrowave.com)  
[sales@fairviewmicrowave.com](mailto:sales@fairviewmicrowave.com)

## Connectors

| Description                   | Connector 1                  | Connector 2                |
|-------------------------------|------------------------------|----------------------------|
| Type                          | TRB 3-Slot Plug Bayonet      | Blunt Cut Genderless Other |
| Option                        | Bend Relief Spring           |                            |
| Impedance                     | 78 Ohms                      |                            |
| Contact Material & Plating    | Bronze, Gold 30 micro inches |                            |
| Contact Plating Spec.         | ASTM-B-488                   |                            |
| Dielectric Type               | Teflon                       |                            |
| Outer Cond Material & Plating | Phosphor Bronze, Gold        |                            |
| Outer Cond Plating Spec.      | 30 micro inches              |                            |
| Body Material & Plating       | Brass, Nickel                |                            |
| Body Plating Spec.            | ASTM-B-733                   |                            |

## Environmental Specifications

### Temperature

Operating Range -55 to +200 deg C

## Compliance Certifications (see [product page](#) for current document)

## Plotted and Other Data

Notes:

## How to Order

Part Number Configuration:

**FM3CA2342 - xx uu**

cm = Centimeters  
 <blank> = Inches

Length

Example: FM3CA2342-12 = 12 inches long cable  
 FM3CA2342-100cm = 100 cm long cable

Bend Relief TRB Plug to Blunt Cut Genderless 1553 Cable 36 Inch Length Using 78 Ohm M17/176-00002 Coax from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: [Bend Relief TRB Plug to Blunt Cut Genderless 1553 Cable 36 Inch Length Using 78 Ohm M17/176-00002 Coax FM3CA2342-36](#)

URL: <https://www.fairviewmicrowave.com/1553-trb-3-slot-plug-to-blunt-cut-genderless-cable-78-ohm-m17-176-00002-coax-in-36-inch-with-bend-relief-fm3ca2342-36-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

