

**TRB Plug Right Angle to TRB Plug  
 Right Angle 1553 Cable 60 Inch Length Using  
 78 Ohm M17/176-00002 Coax**

The 78 ohm RA TRB 3-Slot plug to 78 ohm RA TRB 3-Slot plug 60 inch cable using 78 ohm M17/176-00002 twinax, part number FM3MP2167-60, from Fairview Microwave is in-stock and ships same day. This Fairview TRB 3-Slot to TRB 3-Slot cable assembly has a plug to plug gender configuration with 78 ohm flexible M17/176-00002 twinax. Fairview Microwave's flexible RF cable assemblies are ideal for applications where tight bends and continual flexure are required. The FM3MP2167-60 TRB 3-Slot plug to TRB 3-Slot plug cable assembly operates to 10 MHz. The right angle TRB 3-Slot interfaces on the M17/176-00002 cable allow for easier connections in tight spaces.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

**Electrical Specifications**

Description	Min	Typ	Max	Units
Frequency Range	DC		10	MHz
Capacitance		24 [78.74]		pF/ft [pF/m]
Operating Voltage (AC)			750,000	Vrms

**Performance by Frequency**

Description	F1	F2	F3	F4	F5	Units
Frequency	0.47	0.505	0.54	0.575	0.625	MHz
Insertion Loss (Typ.)	0.47	0.505	0.535	0.57	0.625	dB

**Electrical Specification Notes:**

The Insertion Loss data above is based on the performance specifications of the coax and connectors used in this assembly. The Insertion Loss includes an estimated insertion loss of 0.2 dB per connector.

**Mechanical Specifications**
**Cable Assembly**

Length\* 60 in [152.4 cm]  
 Weight 0.25 lbs [113.4 g]

**Cable**

Cable Type M17/176-00002  
 Impedance 78 Ohms  
 Inner Conductor Type Stranded  
 Inner Conductor Material and Plating Copper, Silver  
 Dielectric Type PTFE  
 Shield Layer 1 Silver Plated Copper  
 Jacket Material PFA, Blue

One Time Minimum Bend Radius 1.5 in [38.1 mm]


**Configuration:**

- TRB 3-Slot Plug Right Angle
- TRB 3-Slot Plug Right Angle
- M17/176-00002

**Features:**

- Max Frequency 10 MHz
- PFA Jacket
- MIL-STD-1553
- -55°C to +200°C
- 78 ohms

**Applications:**

- General Purpose
- Laboratory Use
- Vehicle High Temperature
- Data
- MIL-STD-1553

Fairview Microwave  
 301 Leora Ln., Suite 100  
 Lewisville, TX 75056  
 Tel: 1-800-715-4396 / (972) 649-6678  
 Fax: (972) 649-6689  
[www.fairviewmicrowave.com](http://www.fairviewmicrowave.com)  
[sales@fairviewmicrowave.com](mailto:sales@fairviewmicrowave.com)

**Connectors**

Description	Connector 1	Connector 2
Type	TRB 3-Slot Plug Bayonet	TRB 3-Slot Plug Bayonet
Impedance	78 Ohms	78 Ohms
Contact Material & Plating	Bronze, Gold 30 micro inches	Bronze, Gold 30 micro inches
Contact Plating Spec.	ASTM-B-488	ASTM-B-488
Dielectric Type	Teflon	Teflon
Outer Cond Material & Plating	Phosphor Bronze, Gold	Phosphor Bronze, Gold
Outer Cond Plating Spec.	30 micro inches	30 micro inches
Body Material & Plating	Brass, Nickel	Brass, Nickel
Body Plating Spec.	ASTM-B-733	ASTM-B-733

**Environmental Specifications**  
**Temperature**

Operating Range -55 to +200 deg C

**Compliance Certifications** (see [product page](#) for current document)

**Plotted and Other Data**

Notes:

**How to Order**

Part Number Configuration: **FM3MP2167 - xx uu**

cm = Centimeters  
<blank> = Inches

Length

Example: FM3MP2167-12 = 12 inches long cable  
FM3MP2167-100cm = 100 cm long cable

TRB Plug Right Angle to TRB Plug Right Angle 1553 Cable 60 Inch Length Using 78 Ohm M17/176-00002 Coax from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: [TRB Plug Right Angle to TRB Plug Right Angle 1553 Cable 60 Inch Length Using 78 Ohm M17/176-00002 Coax FM3MP2167-60](#)

URL: <https://www.fairviewmicrowave.com/1553-ra-trb-plug-to-ra-trb-plug-cable-78-ohm-m17-176-00002-coax-in-60-inch-fm3mp2167-60-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

