

78 Ohm Bend Relief 3-Slot TRB Solder/Clamp Plug to Bend Relief 2-Slot TRB Solder/Clamp Plug for M17/176-00002 60" Cable

The 78 ohm TRB 3-Slot plug to 78 ohm TRB 2-Slot plug 60 inch cable using 78 ohm M17/176-00002 twinax, part number FM3MP2232-60, from Fairview Microwave is in-stock and ships same day. This Fairview TRB 3-Slot to TRB 2-Slot cable assembly has a plug to plug gender configuration with 78 ohm flexible M17/176-00002 twinax. Fairview Microwave's flexible RF cable assemblies are ideal for applications where tight bends and continual flexure are required. The FM3MP2232-60 TRB 3-Slot plug to TRB 2-Slot plug cable assembly operates to 10 MHz. The FM3MP2232 cable assembly consists of a Bend Relief 3-slot solder/clamp TRB plug to a Bend Relief 2-slot solder/clamp TRB plug on M17/176-00002 Twinax cable, that is in the High Temperature-rated bus cabling category for MIL-STD-1553 applications. This thicker cable (0.129" O.D.) provides a robust cabling solution with less attenuation per foot. These cable assemblies come with a 1.700" steel spring-style bend relief that helps to minimize cable damage when exceeding the cables minimum bend radius. These assemblies are built to withstand severe shocks and vibrations.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Min	Typ	Max	Units
Frequency Range	DC		10	MHz
Capacitance		24 [78.74]		pF/ft [pF/m]
Operating Voltage (AC)			750,000	Vrms

Performance by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	1	3	5	7	10	MHz
Insertion Loss (Typ.)	0.27	0.305	0.34	0.375	0.425	dB

Electrical Specification Notes:

The Insertion Loss data above is based on the performance specifications of the coax and connectors used in this assembly. The Insertion Loss includes an estimated insertion loss of 0.1 dB per connector.

Mechanical Specifications

Cable Assembly

Length* 60 in [152.4 cm]
Weight 0.367 lbs [166.47 g]

Cable

Cable Type M17/176-00002
Impedance 78 Ohms
Inner Conductor Type Stranded
Inner Conductor Material and Plating Copper, Silver
Dielectric Type PTFE



Configuration:

- TRB 3-Slot Plug
- TRB 2-Slot Plug
- M17/176-00002

Features:

- Max Frequency 10 MHz
- PFA Jacket
- MIL-STD-1553
- -55°C to +200°C
- 78 ohms

Applications:

- General Purpose
- Laboratory Use
- Vehicle High Temperature
- Data
- MIL-STD-1553

Fairview Microwave
301 Leora Ln., Suite 100
Lewisville, TX 75056
Tel: 1-800-715-4396 / (972) 649-6678
Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com

Shield Layer 1 Silver Plated Copper
Jacket Material PFA, Blue

One Time Minimum Bend Radius 1.5 in [38.1 mm]

Connectors

Description	Connector 1	Connector 2
Type	TRB 3-Slot Plug Bayonet	TRB 2-Slot Plug Bayonet
Option	Bend Relief Spring	Bend Relief Spring
Impedance	78 Ohms	78 Ohms
Contact Material & Plating	Bronze, Gold 30 micro inches	Bronze, Gold 30 micro inches
Contact Plating Spec.	ASTM-B-488	ASTM-B-488
Dielectric Type	Teflon	Teflon
Outer Cond Material & Plating	Phosphor Bronze, Gold	Phosphor Bronze, Gold
Outer Cond Plating Spec.	30 micro inches	30 micro inches
Body Material & Plating	Brass, Nickel	Brass, Nickel
Body Plating Spec.	ASTM-B-733	ASTM-B-733

Environmental Specifications
Temperature

Operating Range -55 to +200 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

How to Order

Part Number Configuration:

FM3MP2232 - xx uu

cm = Centimeters
<blank> = Inches
Length

Example: FM3MP2232-12 = 12 inches long cable
FM3MP2232-100cm = 100 cm long cable

78 Ohm Bend Relief 3-Slot TRB Solder/Clamp Plug to Bend Relief 2-Slot TRB Solder/Clamp Plug for M17/176-00002 60" Cable from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: [78 Ohm Bend Relief 3-Slot TRB Solder/Clamp Plug to Bend Relief 2-Slot TRB Solder/Clamp Plug for M17/176-00002 Twinax \(.129 O.D.\) 60" Cable FM3MP2232-60](#)

URL: <https://www.fairviewmicrowave.com/1553-trb-plug-to-trb-plug-cable-78-ohm-m17-176-00002-coax-in-60-inch-fm3mp2232-60-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.



