

1553 TRB 3-Slot Plug to TRB 3-Lug Jack Bulkhead Cable 78 Ohm M17/176-00002 Coax in 24 Inch

The 78 ohm TRB 3-Slot plug to 78 ohm TRB 3-Lug jack bulkhead 24 inch cable using 78 ohm M17/176-00002 twinax, part number FM3MP2252-24, from Fairview Microwave is in-stock and ships same day. This Fairview TRB 3-Slot to TRB 3-Lug cable assembly has a plug to jack gender configuration with 78 ohm flexible M17/176-00002 twinax. Fairview Microwave's flexible RF cable assemblies are ideal for applications where tight bends and continual flexure are required. The FM3MP2252-24 TRB 3-Slot plug to TRB 3-Lug jack cable assembly operates to 10 MHz. Our RF cable assembly with TRB 3-Lug bulkhead interface allows designers to create external connections on their product enclosures, and can be used in a variety of other rack mount and panel mount applications.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Min	Typ	Max	Units
Frequency Range	DC		10	MHz
Capacitance		24 [78.74]		pF/ft [pF/m]
Operating Voltage (AC)			750,000	Vrms

Performance by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	1	3	5	7	10	MHz
Insertion Loss (Typ.)	0.228	0.242	0.256	0.27	0.29	dB

Electrical Specification Notes:

The Insertion Loss data above is based on the performance specifications of the coax and connectors used in this assembly. The Insertion Loss includes an estimated insertion loss of 0.1 dB per connector.

Mechanical Specifications
Cable Assembly

Length* 24 in [609.6 mm]
 Weight 0.213 lbs [96.62 g]

Cable

Cable Type M17/176-00002
 Impedance 78 Ohms
 Inner Conductor Type Stranded
 Inner Conductor Material and Plating Copper, Silver
 Dielectric Type PTFE
 Shield Layer 1 Silver Plated Copper
 Jacket Material PFA, Blue

One Time Minimum Bend Radius 1.5 in [38.1 mm]


Configuration:

- TRB 3-Slot Plug
- TRB 3-Lug Jack Bulkhead
- M17/176-00002

Features:

- Max Frequency 10 MHz
- PFA Jacket
- MIL-STD-1553
- -55°C to +200°C
- 78 ohms

Applications:

- General Purpose
- Laboratory Use
- Vehicle High Temperature
- Data
- MIL-STD-1553

Fairview Microwave
 301 Leora Ln., Suite 100
 Lewisville, TX 75056
 Tel: 1-800-715-4396 / (972) 649-6678
 Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com

Connectors

Description	Connector 1	Connector 2
Type	TRB 3-Slot Plug Bayonet	TRB 3-Lug Jack Bayonet
Mount Method		Bulkhead
Impedance	78 Ohms	78 Ohms
Contact Material & Plating	Bronze, Gold 30 micro inches	Bronze, Gold 30 micro inches
Contact Plating Spec.	ASTM-B-488	ASTM-B-488
Dielectric Type	Teflon	Teflon
Outer Cond Material & Plating	Phosphor Bronze, Gold	Phosphor Bronze, Gold
Outer Cond Plating Spec.	30 micro inches	30 micro inches
Body Material & Plating	Brass, Nickel	Brass, Nickel
Body Plating Spec.	ASTM-B-733	ASTM-B-733

Environmental Specifications
Temperature

Operating Range -55 to +200 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

How to Order

 Part Number Configuration: **FM3MP2252 - xx uu**

 cm = Centimeters
 <blank> = Inches

Length


 Example: FM3MP2252-12 = 12 inches long cable
 FM3MP2252-100cm = 100 cm long cable

1553 TRB 3-Slot Plug to TRB 3-Lug Jack Bulkhead Cable 78 Ohm M17/176-00002 Coax in 24 Inch from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: [1553 TRB 3-Slot Plug to TRB 3-Lug Jack Bulkhead Cable 78 Ohm M17/176-00002 Coax in 24 Inch FM3MP2252-24](#)

URL: <https://www.fairviewmicrowave.com/1553-trb-3-slot-plug-to-trb-3-lug-jack-bulkhead-cable-78-ohm-m17-176-00002-coax-in-24-inch-fm3mp2252-24-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.



REVISION		DATE	CHANGED BY	APPROVED	
ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	INITIAL RELEASE	08/01/2023	LNAGARAJ	EKIM

<p>Fairview Microwave® an INFINITE® brand</p>		<p>INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5</p>	
Website: www.FairviewMicrowave.com Phone: 1.800.715.4396 1.972.649.6678		SCALE	SHEET
DESCRIPTION TRB 3-SLOT SOLDER/CLAMP PLUG TO TRB 3-LUG NON-INSULATED BULKHEAD JACK M17-176-		NONE	1 OF 1
SIZE	CAGE CODE	DRAWN BY	ITEM NO.
A	3FKR5	LNAGARAJ	FM3MP2252-XX

UNLESS OTHERWISE SPECIFIED, DIMENSIONS IN PARENTHESES ARE IN MILLIMETERS

TOLERANCES:

X = ±.02 (51)	FRACTIONS
.XX = ±.02 (51)	±.132
.XXX = ±.06 (1.3)	ANGLES ±1°

CABLE LENGTH TOLERANCES:

>12 (305) ≤ 60 (1524)	±.12 (51) / -0
>60 (1524) ≤ 120 (3048)	±.12 (51) / -0
>120 (3048) ≤ 300 (7620)	±.12 (51) / -0
>300 (7620)	±.12 (51) / -0

ALL DIMENSIONS ARE FOR REFERENCE ONLY AND SUBJECT TO CHANGE WITHOUT NOTICE. UNDIMENSIONED NON-CRITICAL FEATURES MAY VARY FROM DRAWING. DIMENSIONS MAY VARY.

- NOTES:
- CABLE ASSEMBLY LENGTH LABEL PLACEMENT: 36 INCHES OR LESS, ONE LABEL APPROXIMATELY CENTERED. LONGER THAN 36 INCHES, TWO LABELS APPROXIMATELY 6 INCHES FROM EACH CONNECTOR.
 - CABLE ASSEMBLIES SHALL BE TESTED FOR CONTINUITY.
 - CABLE ASSEMBLY LENGTH DETERMINED BY PN AS ILLUSTRATED: FM3MP2252-XX (XX = OAL IN METERS).
- THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. EXPORT ADMINISTRATION REGULATIONS: DIVERSION CONTRARY TO U.S. LAW PROHIBITED.