

Halogen Free 3-Lug TRB Bulkhead Insulated Jack with Blunt Cut for 78 Ohm TWCH-78-2, 36" Cable

The 78 ohm TRB 3-Lug jack bulkhead to Blunt cut genderless 36 inch cable using 78 ohm TWCH-78-2 twinax, part number FM3MSA00402-36, from Fairview Microwave is in-stock and ships same day. This Fairview TRB 3-Lug to Blunt Cut cable assembly has a jack to genderless gender configuration with 78 ohm flexible TWCH-78-2 twinax. Fairview Microwave's flexible RF cable assemblies are ideal for applications where tight bends and continual flexure are required. The FM3MSA00402-36 TRB 3-Lug jack to Blunt cut genderless cable assembly operates to 500 MHz. Our RF cable assembly with TRB 3-Lug bulkhead interface allows designers to create external connections on their product enclosures, and can be used in a variety of other rack mount and panel mount applications.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

| Description | Min | Typ | Max | Units |
|------------------------|-----|--------------|-------|--------------|
| Frequency Range | DC | | 500 | MHz |
| Capacitance | | 21.2 [69.55] | | pF/ft [pF/m] |
| Operating Voltage (AC) | | | 1,000 | Vrms |

Performance by Frequency

| Description | F1 | F2 | F3 | F4 | F5 | Units |
|-------------|----|----|-----|-----|-----|-------|
| Frequency | 10 | 50 | 100 | 200 | 500 | MHz |

Mechanical Specifications

Cable Assembly

| | |
|---------|--------------------|
| Length* | 36 in [914.4 mm] |
| Weight | 0.17 lbs [77.11 g] |

Cable

| | |
|--------------------------------------|----------------------|
| Cable Type | TWCH-78-2 |
| Impedance | 78 Ohms |
| Inner Conductor Type | Stranded |
| Inner Conductor Material and Plating | Copper, Silver |
| Dielectric Type | PE |
| Shield Layer 1 | Silver Plated Copper |
| Jacket Material | HF POF, Blue |

| | |
|------------------------------|------------------|
| One Time Minimum Bend Radius | 1.5 in [38.1 mm] |
|------------------------------|------------------|



Configuration:

- TRB 3-Lug Jack Bulkhead
- Blunt Cut Genderless
- TWCH-78-2

Features:

- Max Frequency 500 MHz
- HF POF Jacket
- MIL-STD-1553
- -30°C to +80°C
- 78 ohms
- Halogen Free
- Non-Toxic

Applications:

- General Purpose
- Laboratory Use
- Military Contractors
- MIL-STD-1553
- Data
- Safer Environments
- Ventilation critical areas

Fairview Microwave
 301 Leora Ln., Suite 100
 Lewisville, TX 75056
 Tel: 1-800-715-4396 / (972) 649-6678
 Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com

Connectors

| Description | Connector 1 | Connector 2 |
|-------------------------------|--|-------------|
| Type | TRB 3-Lug Jack BayonetBlunt Cut Genderless Other | |
| Option | Insulated Bulk Head | |
| Mount Method | Bulkhead | |
| Impedance | 78 Ohms | |
| Contact Material & Plating | Bronze, Gold 30 micro inches | |
| Contact Plating Spec. | ASTM-B-488 | |
| Dielectric Type | Teflon | |
| Outer Cond Material & Plating | Phosphor Bronze, Gold | |
| Outer Cond Plating Spec. | 30 micro inches | |
| Body Material & Plating | Brass, Nickel | |
| Body Plating Spec. | ASTM-B-733 | |

Environmental Specifications

Temperature

Operating Range -30 to +80 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

How to Order

Part Number Configuration: **FM3MSA00402 - xx uu**

Example: FM3MSA00402-12 = 12 inches long cable
FM3MSA00402-100cm = 100 cm long cable



Halogen Free 3-Lug TRB Bulkhead Insulated Jack with Blunt Cut for 78 Ohm TWCH-78-2, 36" Cable from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: [Halogen Free 3-Lug TRB Bulkhead Insulated Jack with Blunt Cut for 78 Ohm TWCH-78-2, 36" Cable FM3MSA00402-36](#)

URL: <https://www.fairviewmicrowave.com/1553-trb-3-lug-jack-bulkhead-to-blunt-cut-genderless-cable-78-ohm-twch-78-2-coax-in-36-inch-fm3msa00402-36-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

