

## TRB 3-Slot Plug to TRB 3-Lug Jack Non-Insulated Bulkhead 1553 Cable 60" Using 124 Ohm TWC-124-2 Twinax

The 78 ohm TRB 3-Slot plug to 78 ohm TRB 3-Lug jack bulkhead 60 cable using 124 ohm TWC-124-2 twinax, part number FM3MSA00653-60, from Fairview Microwave is in-stock and ships same day. This Fairview TRB 3-Slot to TRB 3-Lug cable assembly has a plug to jack gender configuration with 124 ohm flexible TWC-124-2 twinax. Fairview Microwave's flexible RF cable assemblies are ideal for applications where tight bends and continual flexure are required. The FM3MSA00653-60 TRB 3-Slot plug to TRB 3-Lug jack cable assembly operates to 500 MHz. Our RF cable assembly with TRB 3-Lug bulkhead interface allows designers to create external connections on their product enclosures, and can be used in a variety of other rack mount and panel mount applications.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

### Electrical Specifications

| Description            | Min | Typ          | Max   | Units        |
|------------------------|-----|--------------|-------|--------------|
| Frequency Range        | DC  |              | 500   | MHz          |
| Capacitance            |     | 12.3 [40.35] |       | pF/ft [pF/m] |
| Operating Voltage (AC) |     |              | 1,000 | Vrms         |

### Performance by Frequency

| Description           | F1    | F2   | F3    | F4   | F5   | Units |
|-----------------------|-------|------|-------|------|------|-------|
| Frequency             | 10    | 50   | 100   | 200  | 500  | MHz   |
| Insertion Loss (Typ.) | 0.285 | 0.38 | 0.455 | 0.56 | 0.77 | dB    |

#### Electrical Specification Notes:

The Insertion Loss data above is based on the performance specifications of the coax and connectors used in this assembly. The Insertion Loss includes an estimated insertion loss of 0.1 dB per connector.

### Mechanical Specifications

#### Cable Assembly

|         |                     |
|---------|---------------------|
| Length* | 60 in [152.4 cm]    |
| Weight  | 0.293 lbs [132.9 g] |

#### Cable

|                                      |                      |
|--------------------------------------|----------------------|
| Cable Type                           | TWC-124-2            |
| Impedance                            | 124 Ohms             |
| Inner Conductor Type                 | Stranded             |
| Inner Conductor Material and Plating | Copper, Silver       |
| Dielectric Type                      | PE                   |
| Shield Layer 1                       | Silver Plated Copper |
| Jacket Material                      | PVC, Blue            |

|                              |                    |
|------------------------------|--------------------|
| One Time Minimum Bend Radius | 1.25 in [31.75 mm] |
|------------------------------|--------------------|



### Configuration:

- TRB 3-Slot Plug
- TRB 3-Lug Jack Bulkhead
- TWC-124-2

### Features:

- Max Frequency 500 MHz
- PVC Jacket
- 124 ohms
- Twinaxial
- MIL-STD-1553B
- -40°C to +80°C
- Lead Free Solder
- Standard and Custom Lengths Available

### Applications:

- General Purpose
- Laboratory Use
- MIL-STD-1553B Applications
- Data Transmission

Fairview Microwave  
 301 Leora Ln., Suite 100  
 Lewisville, TX 75056  
 Tel: 1-800-715-4396 / (972) 649-6678  
 Fax: (972) 649-6689  
[www.fairviewmicrowave.com](http://www.fairviewmicrowave.com)  
[sales@fairviewmicrowave.com](mailto:sales@fairviewmicrowave.com)

## Connectors

| Description                   | Connector 1                  | Connector 2                  |
|-------------------------------|------------------------------|------------------------------|
| Type                          | TRB 3-Slot Plug Bayonet      | TRB 3-Lug Jack Bayonet       |
| Mount Method                  |                              | Bulkhead                     |
| Specification                 | MIL-STD-1553                 | MIL-STD-1553                 |
| Impedance                     | 78 Ohms                      | 78 Ohms                      |
| Contact Material & Plating    | Bronze, Gold 30 micro inches | Bronze, Gold 30 micro inches |
| Contact Plating Spec.         | ASTM-B-488                   | ASTM-B-488                   |
| Dielectric Type               | Teflon                       | Teflon                       |
| Outer Cond Material & Plating | Phosphor Bronze, Gold        | Phosphor Bronze, Gold        |
| Outer Cond Plating Spec.      | 30 micro inches              | 30 micro inches              |
| Body Material & Plating       | Brass, Nickel                | Brass, Nickel                |
| Body Plating Spec.            | ASTM-B-733                   | ASTM-B-733                   |
| Seal Gasket Material          | Rubber                       |                              |

## Environmental Specifications

### Temperature

Operating Range -40 to +80 deg C

## Compliance Certifications (see [product page](#) for current document)

## Plotted and Other Data

Notes:

## How to Order

Part Number Configuration:

**FM3MSA00653 - xx uu**

cm = Centimeters  
 <blank> = Inches  
 Length

Example: FM3MSA00653-12 = 12 inches long cable  
 FM3MSA00653-100cm = 100 cm long cable

TRB 3-Slot Plug to TRB 3-Lug Jack Non-Insulated Bulkhead 1553 Cable 60" Using 124 Ohm TWC-124-2 Twinax from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: [TRB 3-Slot Plug to TRB 3-Lug Jack Non-Insulated Bulkhead 1553 Cable 60" Using 124 Ohm TWC-124-2 Twinax FM3MSA00653-60](https://www.fairviewmicrowave.com/1553-trb-3-slot-plug-to-trb-3-lug-jack-bulkhead-cable-124-ohm-twc-124-2-coax-in-60-fm3msa00653-60-p.aspx)

URL: <https://www.fairviewmicrowave.com/1553-trb-3-slot-plug-to-trb-3-lug-jack-bulkhead-cable-124-ohm-twc-124-2-coax-in-60-fm3msa00653-60-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.



