

N Male to RA N Male Cable RG-214 Coax in 36 Inch with LF Solder

The type N male to RA type N male 36 inch cable using RG-214 coax, part number FMC0142214LF-36, from Fairview Microwave is in-stock and ships same day. This Fairview type N to type N cable assembly has a male to male gender configuration with 50 ohm flexible RG-214 coax. Fairview Microwave's flexible RF cable assemblies are ideal for applications where tight bends and continual flexure are required. The FMC0142214LF-36 type N male to type N male cable assembly operates to 5 GHz. The right angle type N interface on the RG-214 cable allows for easier connections in tight spaces. The double shielding of this Fairview cable assembly provides excellent shielding effectiveness.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

| Description | Min | Typ | Max | Units |
|-------------------------|-------|----------|--------|--------------|
| Frequency Range | DC | | 5 | GHz |
| VSWR | | | 1.35:1 | |
| Velocity of Propagation | | 66 | | % |
| Capacitance | 30.94 | [101.51] | | pF/ft [pF/m] |

Mechanical Specifications

Cable Assembly

Length* 36 in [914.4 mm]

Cable

Cable Type RG-214
 Impedance 50 Ohms
 Inner Conductor Type Stranded
 Inner Conductor Material and Plating Copper, Silver
 Dielectric Type PE
 Number of Shields 2
 Shield Layer 1 Silver Plated Copper Braid
 Shield Layer 2 Silver Plated Copper Braid
 Jacket Material PVC, Black
 Jacket Diameter 0.425 in [10.8 mm]

Connectors

| Description | Connector 1 | Connector 2 |
|----------------------------|---------------|---------------|
| Type | N Male | N Male |
| Configuration | Straight | Right Angle |
| Impedance | 50 Ohms | 50 Ohms |
| Contact Material & Plating | Brass, Gold | Brass, Gold |
| Body Material & Plating | Brass, Nickel | Brass, Nickel |



Configuration:

- N Male
- N Male Right Angle
- RG-214

Features:

- Max Frequency 5 GHz
- 66% Phase Velocity
- Double Shielded
- PVC Jacket

Applications:

- General Purpose
- Laboratory Use

Fairview Microwave
 301 Leora Ln., Suite 100
 Lewisville, TX 75056
 Tel: 1-800-715-4396 / (972) 649-6678
 Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com

Environmental Specifications

Temperature

Operating Range -55 to +155 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

How to Order

Part Number Configuration:

FMC0142214LF - xx uu

cm = Centimeters
<blank> = Inches
Length


Example: FMC0142214LF-12 = 12 inches long cable
FMC0142214LF-100cm = 100 cm long cable

N Male to RA N Male Cable RG-214 Coax in 36 Inch with LF Solder from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: [N Male to RA N Male Cable RG-214 Coax in 36 Inch with LF Solder FMC0142214LF-36](#)

URL: <https://www.fairviewmicrowave.com/standard-n-male-ra-n-male-cable-rg214-coax-fmc0142214lf-36-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.



| | | | | | |
|---|--------|---|-------|--------------------|-------------|
| FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM | | NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm]. | | | |
| TITLE N Male to RA N Male Cable RG-214 Coax in 36 Inch with LF Solder | | DWG NO FMC0142214LF | | CAGE CODE 3FKR5 | |
| CAD FILE | 101014 | SHEET | SCALE | N/A | SIZE A 5568 |