

SMA Male to SMA Male Cable RG-316 Coax in 12 Inch with LF Solder

The SMA male to SMA male 12 inch cable using RG-316 coax, part number FMC0202315LF-12, from Fairview Microwave is in-stock and ships same day. This Fairview SMA to SMA cable assembly has a male to male gender configuration with 50 ohm flexible RG-316 coax. Fairview Microwave's flexible RF cable assemblies are ideal for applications where tight bends and continual flexure are required. The FMC0202315LF-12 SMA male to SMA male cable assembly operates to 3 GHz.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Min	Typ	Max	Units
Frequency Range	DC		3	GHz
VSWR			1.35:1	
Velocity of Propagation		70		%
Capacitance		32 [104.99]		pF/ft [pF/m]

Mechanical Specifications

Cable Assembly

Length* 12 in [304.8 mm]
 Weight 0.02604 lbs [11.81 g]

Cable

Cable Type RG-316
 Impedance 50 Ohms
 Inner Conductor Type Stranded
 Inner Conductor Material and Plating Copper, Silver
 Dielectric Type PTFE
 Number of Shields 1
 Shield Layer 1 Silver Plated Copper Braid
 Outer Conductor Material and Plating Copper, Silver
 Jacket Material FEP, Tan
 Jacket Diameter 0.098 in [2.49 mm]

One Time Minimum Bend Radius 0.512 in [13 mm]
 Repeated Minimum Bend Radius 12 in [304.8 mm]



Configuration:

- SMA Male
- SMA Male
- RG-316

Features:

- Max Frequency 3 GHz
- 70% Phase Velocity
- FEP Jacket

Applications:

- General Purpose
- Laboratory Use

Fairview Microwave
 301 Leora Ln., Suite 100
 Lewisville, TX 75056
 Tel: 1-800-715-4396 / (972) 649-6678
 Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com

Connectors

Description	Connector 1	Connector 2
Type	SMA Male	SMA Male
Configuration	Straight	Straight
Impedance	50 Ohms	50 Ohms
Contact Material & Plating	Brass, Gold	Brass, Gold
Contact Plating Spec.	50µ in. minimum	50µ in. minimum
Dielectric Type	PTFE	PTFE
Body Material & Plating	Brass, Nickel	Brass, Nickel
Body Plating Spec.	100µ in. minimum	100µ in. minimum
Hex Size	5/16 inch	5/16 inch
Torque	4 in-lbs 0.45 Nm	4 in-lbs 0.45 Nm

Environmental Specifications
Temperature

Operating Range -65 to +165 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

How to Order

 Part Number Configuration: **FMC0202315LF - xx uu**

 cm = Centimeters
 <blank> = Inches

Length


 Example: FMC0202315LF-12 = 12 inches long cable
 FMC0202315LF-100cm = 100 cm long cable

SMA Male to SMA Male Cable RG-316 Coax in 12 Inch with LF Solder from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: [SMA Male to SMA Male Cable RG-316 Coax in 12 Inch with LF Solder FMC0202315LF-12](#)

URL: <https://www.fairviewmicrowave.com/sma-male-sma-male-cable-rg316-coax-fmc0202315lf-12-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.



NOTE:
CABLES 36" AND UNDER HAVE 1 LABEL CENTERED. CABLES OVER 36" HAVE 2 LABELS, ONE AT EACH END, 6.0" FROM THE FRONT OF THE CONNECTOR.

How To Order		Part # Ext.	Length In Inches	Part # Ext.	Length In Centimeters		
<p><u>Part Number Configuration</u></p> <p>FMC zzzzzz - [xx] [uu]</p> <p>cm = Centimeters < Blank > = Inches Length</p>	<u>Examples</u>	-12	12"	-25cm	25cm		
	FMC000-100	-24	24"	-50cm	50cm		
	FMC000-100cm	-36	36"	-75cm	75cm		
		-48	48"	-100cm	100cm		
		-60	60"	-125cm	125cm		
		-xx	Custom Length	-xxcm	Custom Length		
<p>FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM</p>		<p>NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].</p>					
TITLE		DWG NO		CAGE CODE			
SMA Male to SMA Male Cable RG-316 Coax in 12 Inch with LF Solder		FMC0202315LF		3FKR5			
		CAD FILE	092514	SHEET	SCALE	N/A	SIZE