

## SMA Male to SMB Plug Cable RG-316 Coax in 6 Inch with LF Solder

The SMA male to SMB plug 6 inch cable using RG-316 coax, part number FMC0216315LF-06, from Fairview Microwave is in-stock and ships same day. This Fairview SMA to SMB cable assembly has a male to plug gender configuration with 50 ohm flexible RG-316 coax. Fairview Microwave's flexible RF cable assemblies are ideal for applications where tight bends and continual flexure are required. The FMC0216315LF-06 SMA male to SMB plug cable assembly operates to 3 GHz.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

### Electrical Specifications

Description	Min	Typ	Max	Units
Frequency Range	DC		3	GHz
VSWR			1.35:1	
Velocity of Propagation		70	%	
Capacitance		32 [104.99]		pF/ft [pF/m]

### Mechanical Specifications

#### Cable Assembly

Length*	6 in [152.4 mm]
Weight	0.033 lbs [14.97 g]

#### Cable

Cable Type	RG-316
Impedance	50 Ohms
Inner Conductor Type	Solid
Inner Conductor Material and Plating	Copper, Silver
Dielectric Type	PTFE
Number of Shields	1
Shield Layer 1	Silver Plated Copper Braid
Jacket Material	FEP, Tan
Jacket Diameter	0.098 in [2.49 mm]



### Configuration:

- SMA Male
- SMB Plug
- RG-316

### Features:

- Max Frequency 3 GHz
- 70% Phase Velocity
- FEP Jacket

### Applications:

- General Purpose
- Laboratory Use

## Connectors

Description	Connector 1	Connector 2
Type	SMA Male	SMB Plug
Configuration	Straight	Straight
Impedance	50 Ohms	50 Ohms
Contact Material & Plating	Brass, Gold	Beryllium Copper, Gold
Contact Plating Spec.	50 $\mu$ in. minimum	30 $\mu$ in. minimum
Dielectric Type	PTFE	PTFE
Body Material & Plating	Brass, Nickel	Brass, Gold
Body Plating Spec.	100 $\mu$ in. minimum	3 $\mu$ in. minimum
Hex Size	5/16 inch	
Torque	4 in-lbs 0.45 Nm	

## Environmental Specifications

### Temperature

Operating Range -65 to +165 deg C

## Compliance Certifications

(see [product page](#) for current document)

## Plotted and Other Data

Notes:

## How to Order

Part Number Configuration:

**FMC0216315LF - xx uu**

cm = Centimeters

<blank> = Inches

Length


Example: FMC0216315LF-12 = 12 inches long cable  
FMC0216315LF-100cm = 100 cm long cable

SMA Male to SMB Plug Cable RG-316 Coax in 6 Inch with LF Solder from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: [SMA Male to SMB Plug Cable RG-316 Coax in 6 Inch with LF Solder FMC0216315LF-06](#)

URL: <https://www.fairviewmicrowave.com/standard-sma-male-smb-plug-cable-rg316-coax-fmc0216315lf-06-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.



<b>FAIRVIEW MICROWAVE INC.</b> ALLEN, TX 75013 <a href="http://WWW.FAIRVIEWMICROWAVE.COM">WWW.FAIRVIEWMICROWAVE.COM</a>	<small>NOTES:</small> 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].					
	<small>TITLE</small> SMA Male to SMB Plug Cable RG-316 Coax in 6 Inch with LF Solder	<small>DWG NO</small> <b>FMC0216315LF</b>	<small>CAGE CODE</small> <b>3FKR5</b>			