

RA SMA Male to RA SMP Female Cable FM-F086 Coax in 48 Inch

Electrical Specifications

Description	Min	Typ	Max	Units
Frequency Range	DC		12	GHz
VSWR			1.35:1	
Velocity of Propagation		70.6		%
Capacitance		28.95 [94.98]		pF/ft [pF/m]

Mechanical Specifications

Cable Assembly

Length 48 in [121.92 cm]

Cable

Cable Type FM-F086
 Impedance 50 Ohms
 Inner Conductor Type Solid
 Inner Conductor Material and Plating Copper, Silver
 Dielectric Type PTFE
 Number of Shields 2
 Shield Layer 1 Silver Plated Copper Tape
 Shield Layer 2 Silver Plated Copper Braid
 Jacket Material FEP, Blue
 Jacket Diameter 0.209 in [5.31 mm]

Connectors

Description	Connector 1	Connector 2
Type	SMA Male Right Angle	SMP Female Right Angle
Impedance	50 Ohms	50 Ohms
Contact Material & Plating	Brass, Gold	Beryllium Copper, Gold
Contact Plating Spec.	50µ in. minimum	MIL-G-45204
Dielectric Type	Teflon	PTFE
Hex Size	5/16 inch	
Torque	8.5 in-lbs [0.96 Nm]	
Body Material & Plating	Stainless Steel, Gold	Beryllium Copper, Gold
Body Plating Spec.	3µ in. minimum	MIL-G-45204

Environmental Specifications

Temperature

Operating Range -65 to +165 deg C

Compliance Certifications (visit www.FairviewMicrowave.com for current document)

Plotted and Other Data

Notes:




Configuration:

- SMA Male Right Angle
- SMP Female Right Angle
- FM-F086

Fairview Microwave
 1130 Junction Dr. #100
 Allen, TX 75013
 Tel: 1-800-715-4396 / (972) 649-6678
 Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com

Typical Performance Data



How to Order

Part Number Configuration:

FMC0421085 - xx uu

cm = Centimeters
 <blank> = Inches
 Length


Example: FMC0421085-12 = 12 inches long cable
 FMC0421085-100cm = 100 cm long cable

RA SMA Male to RA SMP Female Cable FM-F086 Coax in 48 Inch from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: [RA SMA Male to RA SMP Female Cable FM-F086 Coax in 48 Inch FMC0421085-48](#)

URL: <http://www.fairviewmicrowave.com/ra-sma-male-ra-smp-female-cable-hs086-coax-fmc0421085-48-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.



FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM		NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].			
TITLE RA SMA Male to RA SMP Female Cable FM-F086 Coax in 48 Inch		DWG NO FMC0421085-XX		CAGE CODE 3FKR5	
		CAD FILE 102114	SHEET	SCALE N/A	SIZE A 5568