

MCX Plug to BNC Female Bulkhead Cable
RG-316 Coax

Electrical Specifications

Description	Min	Typ	Max	Units
Frequency Range	DC		3	GHz
VSWR			1.35:1	
Velocity of Propagation		70		%
Capacitance		32 [104.99]		pF/ft [pF/m]

Mechanical Specifications

Cable Assembly

Diameter	0.689 in [17.5 mm]
Weight	0.04145 lbs [18.8 g]

Cable

Cable Type	RG-316
Impedance	50 Ohms
Inner Conductor Type	Solid
Inner Conductor Material and Plating	Copper, Silver
Dielectric Type	PTFE
Number of Shields	1
Shield Layer 1	Silver Plated Copper Braid
Jacket Material	FEP, Tan
Jacket Diameter	0.098 in [2.49 mm]

Connectors

Description	Connector 1	Connector 2
Type	MCX Plug	BNC Female
Polarity	Standard	Standard
Mount Method		Bulkhead
Impedance	50 Ohms	50 Ohms
Contact Material & Plating	Brass, Gold	Beryllium Copper, Gold
Contact Plating Spec.	30µ" Min	50µ in. minimum
Dielectric Type	PTFE	PTFE
Body Material & Plating	Brass, Gold	Brass, Nickel
Body Plating Spec.	3µ" Minimum	3µ in. minimum

Environmental Specifications

Temperature

Operating Range	-55 to +155 deg C
-----------------	-------------------

Compliance Certifications (visit www.FairviewMicrowave.com for current document)

Plotted and Other Data

Notes:




Configuration:

- MCX Plug
- BNC Female Bulkhead
- RG-316

Fairview Microwave
 1130 Junction Dr. #100
 Allen, TX 75013
 Tel: 1-800-715-4396 / (972) 649-6678
 Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com

Typical Performance Data



How to Order

Part Number Configuration:

FMC0738315 - xx uu

cm = Centimeters
 <blank> = Inches
 Length


Example: FMC0738315-12 = 12 inches long cable
 FMC0738315-100cm = 100 cm long cable

MCX Plug to BNC Female Bulkhead Cable RG-316 Coax from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: [MCX Plug to BNC Female Bulkhead Cable RG-316 Coax FMC0738315](#)

URL: <http://www.fairviewmicrowave.com/mcx-plug-bnc-female-cable-rg-316-coax-fmc0738315-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.



FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM		NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].			
TITLE MCX Plug to BNC Female Bulkhead Cable RG-316 Coax		DWG NO <p style="text-align: center; margin: 0;">FMC0738315</p>		CAGE CODE <p style="text-align: center; margin: 0;">3FKR5</p>	
CAD FILE 102114		SHEET	SCALE N/A	SIZE A	5568