

BNC Male to MMCX Plug Cable RG-316 Coax in 48 Inch with LF Solder

The BNC male to MMCX plug 48 inch cable using RG-316 coax, part number FMC0809315LF-48, from Fairview Microwave is in-stock and ships same day. This Fairview BNC to MMCX cable assembly has a male to plug gender configuration with 50 ohm flexible RG-316 coax. Fairview Microwave's flexible RF cable assemblies are ideal for applications where tight bends and continual flexure are required. The FMC0809315LF-48 BNC male to MMCX plug cable assembly operates to 3 GHz.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

| Description | Min | Typ | Max | Units |
|-------------------------|-----|-------------|--------|--------------|
| Frequency Range | DC | | 3 | GHz |
| VSWR | | | 1.35:1 | |
| Velocity of Propagation | | 70 | | % |
| Capacitance | | 32 [104.99] | | pF/ft [pF/m] |


Mechanical Specifications

Cable Assembly

| | |
|---------|-----------------------|
| Length* | 48 in [121.92 cm] |
| Weight | 0.06708 lbs [30.43 g] |

Cable

| | |
|--------------------------------------|----------------------------|
| Cable Type | RG-316 |
| Impedance | 50 Ohms |
| Inner Conductor Type | Stranded |
| Inner Conductor Material and Plating | Copper, Silver |
| Dielectric Type | PTFE |
| Number of Shields | 1 |
| Shield Layer 1 | Silver Plated Copper Braid |
| Jacket Material | FEP, Tan |
| Jacket Diameter | 0.098 in [2.49 mm] |



Configuration:

- BNC Male
- MMCX Plug
- RG-316

Features:

- Max Frequency 3 GHz
- 70% Phase Velocity
- FEP Jacket

Applications:

- General Purpose
- Laboratory Use

Fairview Microwave
 301 Leora Ln., Suite 100
 Lewisville, TX 75056
 Tel: 1-800-715-4396 / (972) 649-6678
 Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com

Connectors

| Description | Connector 1 | Connector 2 |
|----------------------------|------------------|-----------------|
| Type | BNC Male | MMCX Plug |
| Configuration | Straight | Straight |
| Impedance | 50 Ohms | 50 Ohms |
| Contact Material & Plating | Brass, Gold | Brass, Gold |
| Contact Plating Spec. | 50μ in. minimum | 30μ in. minimum |
| Dielectric Type | PTFE | PTFE |
| Body Material & Plating | Brass, Nickel | Brass, Gold |
| Body Plating Spec. | 100μ in. minimum | 3μ in. minimum |

Environmental Specifications

Temperature

Operating Range -65 to +165 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

How to Order

Part Number Configuration: **FMC0809315LF - xx uu**

cm = Centimeters
 <blank> = Inches

Length


Example: FMC0809315LF-12 = 12 inches long cable
 FMC0809315LF-100cm = 100 cm long cable

BNC Male to MMCX Plug Cable RG-316 Coax in 48 Inch with LF Solder from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: [BNC Male to MMCX Plug Cable RG-316 Coax in 48 Inch with LF Solder FMC0809315LF-48](#)

URL: <https://www.fairviewmicrowave.com/standard-bnc-male-mmcx-plug-cable-rg316-coax-fmc0809315lf-48-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.



| | | | | | |
|---|--------|---|-------|--------------------|-------------|
| FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM | | NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm]. | | | |
| TITLE BNC Male to MMCX Plug Cable RG-316 Coax in 48 Inch with LF Solder | | DWG NO FMC0809315LF | | CAGE CODE 3FKR5 | |
| CAD FILE | 102114 | SHEET | SCALE | N/A | SIZE A 5568 |