

**MMCX Plug to SMB Plug Cable RG-316 Coax in 24 Inch**

**Electrical Specifications**

Description	Min	Typ	Max	Units
Frequency Range	DC		2	GHz
VSWR			1.35:1	
Velocity of Propagation		70		%
Capacitance		32 [104.99]		pF/ft [pF/m]

**Mechanical Specifications**

**Cable Assembly**

Length 24 in [609.6 mm]

**Cable**

Cable Type RG-316  
 Impedance 50 Ohms  
 Inner Conductor Type Solid  
 Inner Conductor Material and Plating Copper, Silver  
 Dielectric Type PTFE  
 Number of Shields 1  
 Shield Layer 1 Silver Plated Copper Braid  
 Jacket Material FEP, Tan  
 Jacket Diameter 0.098 in [2.49 mm]

**Connectors**

Description	Connector 1	Connector 2
Type	MMCX Plug	SMB Plug
Impedance	50 Ohms	50 Ohms
Contact Material & Plating	Beryllium Copper, Gold	Beryllium Copper, Gold
Contact Plating Spec.	30μ in. minimum	30μ in. minimum
Dielectric Type	PTFE	PTFE
Body Material & Plating	Brass, Gold	Brass, Gold
Body Plating Spec.	3μ in. minimum	3μ in. minimum

**Environmental Specifications**

**Temperature**

Operating Range -65 to +165 deg C

**Compliance Certifications** (visit [www.FairviewMicrowave.com](http://www.FairviewMicrowave.com) for current document)

**Plotted and Other Data**

Notes:




**Configuration:**

- MMCX Plug
- SMB Plug
- RG-316

Fairview Microwave  
 1130 Junction Dr. #100  
 Allen, TX 75013  
 Tel: 1-800-715-4396 / (972) 649-6678  
 Fax: (972) 649-6689  
[www.fairviewmicrowave.com](http://www.fairviewmicrowave.com)  
[sales@fairviewmicrowave.com](mailto:sales@fairviewmicrowave.com)

**Typical Performance Data**



**How to Order**

Part Number Configuration:

**FMC0916315 - xx uu**

cm = Centimeters  
 <blank> = Inches  
 Length


Example: FMC0916315-12 = 12 inches long cable  
 FMC0916315-100cm = 100 cm long cable

MMCX Plug to SMB Plug Cable RG-316 Coax in 24 Inch from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: [MMCX Plug to SMB Plug Cable RG-316 Coax in 24 Inch FMC0916315-24](#)

URL: <http://www.fairviewmicrowave.com/mmcx-male-smb-plug-cable-rg316-coax-fmc0916315-24-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.



<b>FAIRVIEW MICROWAVE INC.</b> ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM		NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].			
TITLE MMCX Plug to SMB Plug Cable RG-316 Coax in 24 Inch		DWG NO FMC0916315-XX		CAGE CODE 3FKR5	
CAD FILE	102814	SHEET	SCALE	N/A	SIZE A 5568