

SMA Female to SSMC Plug Cable RG-316 Coax in 48 Inch with LF Solder

The SMA female to SSMC plug 48 inch cable using RG-316 coax, part number FMC1334315LF-48, from Fairview Microwave is in-stock and ships same day. This Fairview SMA to SSMC cable assembly has a female to plug gender configuration with 50 ohm flexible RG316 coax. Fairview Microwave's flexible RF cable assemblies are ideal for applications where tight bends and continual flexure are required. The FMC1334315LF-48 SMA female to SSMC plug cable assembly operates to 3 GHz.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Min	Typ	Max	Units
Frequency Range	DC		3	GHz
VSWR			1.35:1	
Velocity of Propagation		70		%
Capacitance		32 [104.99]		pF/ft [pF/m]

Mechanical Specifications

Cable Assembly

Length*	48 in [121.92 cm]
Weight	0.054 lbs [24.49 g]

Cable

Cable Type	RG316
Impedance	50 Ohms
Inner Conductor Type	Solid
Inner Conductor Material and Plating	Copper, Silver
Dielectric Type	PTFE
Number of Shields	1
Shield Layer 1	Silver Plated Copper Braid
Jacket Material	FEP, Tan
Jacket Diameter	0.098 in [2.49 mm]



Configuration:

- SMA Female
- SSMC Plug
- RG316


Features:

- Max Frequency 3 GHz
- 70% Phase Velocity
- FEP Jacket

Applications:

- General Purpose
- Laboratory Use

Cable Diagram:



Fairview Microwave
301 Leora Ln., Suite 100
Lewisville, TX 75056
Tel: 1-800-715-4396 / (972) 649-6678
Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com

Connectors

Description	Connector 1	Connector 2
Type	SMA Female	SSMC Plug
Impedance	50 Ohms	50 Ohms
Mating Cycles		500
Contact Material & Plating	Beryllium Copper, Gold	Beryllium Copper, Gold
Contact Plating Spec.	50μ in. minimum	MIL-G-45204
Dielectric Type	PTFE	PTFE
Body Material & Plating	Brass, Gold	Beryllium Copper, Gold
Body Plating Spec.	3μ in. minimum	
Coupling Nut Material & Plating		Brass, Gold
Hex Size	1/4 inch	5/32 inch

Environmental Specifications

Temperature

Operating Range -65 to +165 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

How to Order

Part Number Configuration: **FMC1334315LF - xx uu**

cm = Centimeters

<blank> = Inches

Length


Example: FMC1334315LF-12 = 12 inches long cable
 FMC1334315LF-100cm = 100 cm long cable

SMA Female to SSMC Plug Cable RG-316 Coax in 48 Inch with LF Solder from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: [SMA Female to SSMC Plug Cable RG-316 Coax in 48 Inch with LF Solder FMC1334315LF-48](#)

URL: <https://www.fairviewmicrowave.com/sma-female-ssmc-plug-cable-rg316-coax-fmc1334315lf-48-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.



FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM		NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].			
TITLE SMA Female to SSMC Plug Cable RG-316 Coax in 48 Inch with LF Solder		DWG NO FMC1334315LF		CAGE CODE 3FKR5	
CAD FILE	101414	SHEET	SCALE	N/A	SIZE A 5568