

Non-Magnetic 2.92mm Male to SMA Male Cable FM-SR047CU-NM Coax



FMCA100383

Configuration

- Connector 1: 2.92mm Male
- Connector 2: SMA Male
- Cable Type: FM-SR047CU-NM
- Coax Flex Type: Semi-Rigid

Features

- Max Frequency 32 GHz
- Shielding Effectivity > 165 dB
- 69.5% Phase Velocity

Applications

- General Purpose
- Laboratory Use

Description

The 2.92mm male to SMA male cable using FM-SR047CU-NM coax, part number FMCA100383, from Fairview Microwave is in-stock and ships same day. This Fairview 2.92mm to SMA cable assembly has a male to male gender configuration with 50 ohm semi-rigid FM-SR047CU-NM coax. Fairview Microwave's semi-rigid RF cable assemblies are ideal for high performance applications and can be formed, using proper tooling, to the routing pattern required. The FMCA100383 2.92mm male to SMA male cable assembly operates to 32 GHz.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		32	GHz
VSWR			1.4:1	
Velocity of Propagation		69.5		%
RF Shielding	165			dB

Specifications by Frequency

Non-Magnetic 2.92mm Male to SMA Male Cable FM-SR047CU-NM Coax

FMCA100383



Part Number	Length	Description	F1	F2	F3	F4	F5	Units	Weight (lbs)
		Frequency	2500	5000	10000	18000	32000	MHz	
FMCA100383	Custom Lengths Available	Insertion Loss (Typ.)	0.508	0.79	1.14	1.56	2.14	dB/ft	
			1.67	2.6	3.75	5.12	7.03	dB/m	
FMCA100383-6	6 inch	Insertion Loss (Typ.)	0.35	0.53	0.76	1.04	1.41	dB	0.202
FMCA100383-9	9 inch	Insertion Loss (Typ.)	0.48	0.73	1.05	1.43	1.95	dB	0.203
FMCA100383-12	12 inch	Insertion Loss (Typ.)	0.61	0.93	1.33	1.82	2.48	dB	0.204
FMCA100383-18	18 inch	Insertion Loss (Typ.)	0.86	1.32	1.9	2.6	3.55	dB	0.207
FMCA100383-24	24 inch	Insertion Loss (Typ.)	1.12	1.72	2.47	3.38	4.62	dB	0.209

The insertion loss data for the base model does not include loss due to the connectors. Each length includes insertion loss due to the connectors.

Loss due to Connector 1: 0.03*SQRT(FGHz) dB
 Loss due to Connector 2: 0.03*SQRT(FGHz) dB
 Base Weight: 0.204 pounds
 Additional Weight per Inch: 0.00034 pounds

Mechanical Specifications

Cable Assembly

Width/Diameter 0.5 in [12.7 mm]
 Weight 0.204 lbs [92.53 g]

Cable

Cable Type FM-SR047CU-NM
 Impedance 50 Ohms
 Inner Conductor Material and Plating Copper, Silver
 Dielectric Type PTFE
 Outer Conductor 1 Material and Plating Copper
 One Time Minimum Bend Radius 0.05 in [1.27 mm]

Connectors

Description	Connector 1	Connector 2
Type	2.92mm Male	SMA Male
Impedance	50 Ohms	50 Ohms
Configuration	Straight	Straight
Contact Material and Plating	Beryllium Copper, Gold	Beryllium Copper, Gold
Dielectric Type	PEI	PTFE
Body Material and Plating	Beryllium Copper, Gold	Beryllium Copper, Gold
Coupling Nut Material and Plating	Beryllium Copper, Gold	Beryllium Copper, Gold
Torque		7 in-lbs 0.79 Nm

Non-Magnetic 2.92mm Male to SMA Male Cable FM-SR047CU-NM Coax



FMCA100383

Environmental Specifications

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Typical Performance Data

How to Order

Part Number Configuration:

FMCA100383

- xx

uu

Unit of Measure:
cm = Centimeters
<blank> = Inches
Length
Base Number

Example: FMCA100383-12 = 12 inches long cable
FMCA100383-100cm = 100 cm long cable

Non-Magnetic 2.92mm Male to SMA Male Cable FM-SR047CU-NM Coax from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [Non-Magnetic 2.92mm Male to SMA Male Cable FM-SR047CU-NM Coax FMCA100383](#)

URL: <https://www.fairviewmicrowave.com/non-magnetic-2.92mm-male-to-sma-male-cable-fm-sr047cu-nm-coax-fm-ca100383-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume liability arising out of the use of any part or document.

