

## 2.92mm Male to 2.92mm Male Cable FM-F086HP Coax in 48 Inch with LF Solder

The 2.92mm male to 2.92mm male 48 inch cable using FM-F086HP coax, part number FMCA1222LF-48, from Fairview Microwave is in-stock and ships same day. This Fairview 2.92mm to 2.92mm cable assembly has a male to male gender configuration with 50 ohm flexible FM-F086HP coax. Fairview Microwave's flexible RF cable assemblies are ideal for applications where tight bends and continual flexure are required. The FMCA1222LF-48 2.92mm male to 2.92mm male cable assembly operates to 40 GHz. The double shielding of this Fairview cable assembly provides excellent shielding effectiveness.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

### Electrical Specifications

| Description             | Min | Typ        | Max   | Units        |
|-------------------------|-----|------------|-------|--------------|
| Frequency Range         | DC  |            | 40    | GHz          |
| VSWR                    |     |            | 1.5:1 |              |
| Velocity of Propagation |     | 76         |       | %            |
| Capacitance             |     | 27 [88.58] |       | pF/ft [pF/m] |

### Mechanical Specifications

#### Cable Assembly

|         |                     |
|---------|---------------------|
| Length* | 48 in [121.92 cm]   |
| Weight  | 0.076 lbs [34.47 g] |

#### Cable

|                                      |                            |
|--------------------------------------|----------------------------|
| Cable Type                           | FM-F086HP                  |
| Impedance                            | 50 Ohms                    |
| Inner Conductor Type                 | Solid                      |
| Inner Conductor Material and Plating | Copper, Silver             |
| Dielectric Type                      | PTFE                       |
| Number of Shields                    | 2                          |
| Shield Layer 1                       | Silver Plated Copper Tape  |
| Shield Layer 2                       | Silver Plated Copper Braid |
| Jacket Material                      | FEP, Blue                  |
| Jacket Diameter                      | 0.105 in [2.67 mm]         |



### Configuration:

- 2.92mm Male
- 2.92mm Male
- FM-F086HP

### Features:

- Max Frequency 40 GHz
- 76% Phase Velocity
- Double Shielded
- FEP Jacket
- 500 Mating Cycles

### Applications:

- General Purpose
- Laboratory Use

Fairview Microwave  
 301 Leora Ln., Suite 100  
 Lewisville, TX 75056  
 Tel: 1-800-715-4396 / (972) 649-6678  
 Fax: (972) 649-6689  
[www.fairviewmicrowave.com](http://www.fairviewmicrowave.com)  
[sales@fairviewmicrowave.com](mailto:sales@fairviewmicrowave.com)

## Connectors

| Description                     | Connector 1                | Connector 2                |
|---------------------------------|----------------------------|----------------------------|
| Type                            | 2.92mm Male                | 2.92mm Male                |
| Impedance                       | 50 Ohms                    | 50 Ohms                    |
| Mating Cycles                   | 500                        | 500                        |
| Contact Material & Plating      | Beryllium Copper, Gold     | Beryllium Copper, Gold     |
| Contact Plating Spec.           | 50μ in. minimum            | 50μ in. minimum            |
| Body Material & Plating         | Beryllium Copper, Gold     | Beryllium Copper, Gold     |
| Body Plating Spec.              | 50μ in. minimum            | 50μ in. minimum            |
| Coupling Nut Material & Plating | Passivated Stainless Steel | Passivated Stainless Steel |
| Hex Size                        | 5/16 inch                  | 5/16 inch                  |
| Torque                          | 8 in-lbs 0.9 Nm            | 8 in-lbs 0.9 Nm            |

## Environmental Specifications

### Temperature

Operating Range -65 to +165 deg C

## Compliance Certifications (see [product page](#) for current document)

## Plotted and Other Data

Notes:

## How to Order

Part Number Configuration: **FMCA1222LF - xx uu**

cm = Centimeters  
 <blank> = Inches

Length


Example: FMCA1222LF-12 = 12 inches long cable  
 FMCA1222LF-100cm = 100 cm long cable

2.92mm Male to 2.92mm Male Cable FM-F086HP Coax in 48 Inch with LF Solder from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: [2.92mm Male to 2.92mm Male Cable FM-F086HP Coax in 48 Inch with LF Solder FMCA1222LF-48](#)

URL: <https://www.fairviewmicrowave.com/standard-2.92mm-male-2.92mm-male-cable-fmf086hp-coax-fmca1222lf-48-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.



|   |        |   |       |                    |             |
|---|--------|---|-------|--------------------|-------------|
| <b>FAIRVIEW MICROWAVE INC.</b><br>ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM           |        | NOTES:<br>1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.<br>2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.<br>3. DIMENSIONS ARE IN INCHES [mm]. |       |                    |             |
| TITLE<br>2.92mm Male to 2.92mm Male Cable FM-F086HP Coax<br>in 48 Inch with LF Solder |        | DWG NO<br>FMCA1222LF  |       | CAGE CODE<br>3FKR5 |             |
| CAD FILE  | 103114 | SHEET   | SCALE | N/A                | SIZE A 5568 |