

## SMA Female to SMA Female Cable RG405 Coax in 18 Inch

Fairview's semi-rigid cable assemblies are convenient ready-to-use cables designed for bench testing, test fixtures, high isolation semi-rigid connections and other microwave semi-rigid cabling purposes. These cables are constructed with high quality semi-rigid coax and SMA Female connectors. These semi-rigid cable assemblies are available in standard straight lengths or custom lengths that can be specified at the time of order. Each semi-rigid cable assembly has been RF tested to ensure performance over the high frequency band.

### Electrical Specifications

Description	Min	Typ	Max	Units
Frequency Range	DC		18	GHz
Dielectric Withstanding Voltage (AC)			1,000	Vrms

### Performance by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	1	2	4.5	9	18	GHz
Insertion Loss (Typ.)	0.53	0.627	0.868	1.303	1.88	dB

#### Electrical Specification Notes:

Insertion Loss does not include the loss of the connectors. Insertion Loss is estimated as 0.1 dB per connector.

### Mechanical Specifications

#### Cable Assembly

Length\* 18 in [457.2 mm]  
Diameter 0.25 in [6.35 mm]

#### Cable

Cable Type RG405/U  
Impedance 50 Ohms  
Inner Conductor Type Solid  
Inner Conductor Material and Plating Copper Clad Steel, Silver  
Dielectric Type PTFE  
Number of Shields 1  
Shield Layer 1 Copper

#### Connectors

Description	Connector 1	Connector 2
Type	SMA Female	SMA Female
Impedance	50 Ohms	50 Ohms
Contact Material & Plating	Gold	Gold
Dielectric Type	PTFE	PTFE
Body Material & Plating	Stainless Steel, Gold	Stainless Steel, Gold



### Configuration:

- SMA Female
- SMA Female
- RG405/U

### Features:

- High performance semi-rigid cable
- 18 GHz performance
- Gold plated connectors
- Same day shipment

### Applications:

- System bench testing
- High isolation connections
- RF susceptibility testing
- Test fixtures

Fairview Microwave  
1130 Junction Dr. #100  
Allen, TX 75013  
Tel: 1-800-715-4396 / (972) 649-6678  
Fax: (972) 649-6689  
[www.fairviewmicrowave.com](http://www.fairviewmicrowave.com)  
[sales@fairviewmicrowave.com](mailto:sales@fairviewmicrowave.com)

Mechanical Specification Notes:

\*All cable assemblies have a length tolerance of 1.5% or  $\pm 3/8"$ , whichever is greater.

**Compliance Certifications** (see [product page](#) for current document)

**Plotted and Other Data**

Notes:

- Values at 25°C, sea level.

**How to Order**

Part Number Configuration:

**FMCA1555 - xx uu**

cm = Centimeters  
 <blank> = Inches  
 Length


Example: FMCA1555-12 = 12 inches long cable  
 FMCA1555-100cm = 100 cm long cable

SMA Female to SMA Female Cable RG405 Coax in 18 Inch from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: [SMA Female to SMA Female Cable RG405 Coax in 18 Inch FMCA1555-18](#)

URL: <https://www.fairviewmicrowave.com/sma-female-sma-female-cable-rg405u-coax-fmca1555-18-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.



STANDARD TOLERANCES	
.X	±0.2
.XX	±0.01
.XXX	±0.005

\*STANDARD TOLERANCES APPLY ONLY TO DIMENSIONS IN INCHES

<b>FAIRVIEW MICROWAVE INC.</b> ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM		NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].			
TITLE SMA Female to SMA Female Cable RG405 Coax in 18 Inch		DWG NO FMCA1555		CAGE CODE 3FKR5	
CAD FILE	091517	SHEET	1 OF 1	SCALE	N/A
				SIZE	A
					7361