

RA MMCX Plug to RA SMA Male Cable RG405 Type .086 Coax in 12 Inch



FMCA2975-12

Configuration

- Connector 1: MMCX Plug Right Angle
- Connector 2: SMA Male Right Angle
- Cable Type: FM-SR086CU-STR
- Coax Flex Type: Semi-Rigid

Features

- Max Frequency 6 GHz

Applications

- General Purpose
- Laboratory Use

Description

The RA MMCX plug to RA SMA male 12 inch cable using RG405 type .086 coax, part number FMCA2975-12, from Fairview Microwave is in-stock and ships same day. This Fairview MMCX to SMA cable assembly has a plug to male gender configuration with 50 ohm semi-rigid FM-SR086CU-STR coax. Fairview Microwave's semi-rigid RF cable assemblies are ideal for high performance applications and can be formed, using proper tooling, to the routing pattern required. The FMCA2975-12 MMCX plug to SMA male cable assembly operates to 6 GHz. The right angle MMCX and right angle SMA interfaces on the FM-SR086CU-STR cable allow for easier connections in tight spaces.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		6	GHz
VSWR			1.5:1	

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	0.25	0.5	1	2.5	6	GHz
Insertion Loss (Typ.)	0.46	0.51	0.62	0.72	0.95	dB

Electrical Specification Notes:

The Insertion Loss data above is based on the performance specifications of the coax and connectors used in this assembly. The Insertion Loss includes an estimated insertion loss of 0.2 dB per connector.

Mechanical Specifications

Cable Assembly

Length 12 in [304.8 mm]
Width/Diameter 0.5 in [12.7 mm]

RA MMCX Plug to RA SMA Male Cable RG405 Type .086 Coax in 12 Inch

FMCA2975-12



Weight	0.032 lbs [14.51 g]
Cable	
Cable Type	FM-SR086CU-STR
Impedance	50 Ohms
Inner Conductor Type	Solid
Inner Conductor Material and Plating	Copper Clad Steel, Silver
Dielectric Type	PTFE
Number of Shields	1
Outer Conductor 1 Material and Plating	Copper
Jacket Material	Tan
Repeated Minimum Bend Radius	0.05 in [1.27 mm]

Connectors

Description	Connector 1	Connector 2
Type	MMCX Plug Right Angle	SMA Male Right Angle
Specification		MIL-STD-348A
Impedance	50 Ohms	50 Ohms
Configuration	Right Angle	Right Angle
Contact Material and Plating	Phosphor Bronze, Gold over Nickel	Brass, Gold
Contact Plating Specification		50 µin minimum
Dielectric Type	PTFE	PTFE
Body Material and Plating	Brass, Gold over Nickel	Stainless Steel, Gold
Body Plating Specification		30 µin minimum
Coupling Nut Material and Plating		Brass, Nickel
Coupling Nut Plating Specification		100 µin minimum
Hex Size		5/16 inch
Torque		3 in-lbs 0.34 Nm

Environmental Specifications

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

RA MMCX Plug to RA SMA Male Cable RG405 Type .086 Coax in 12 Inch



FMCA2975-12

Typical Performance Data

How to Order

Part Number Configuration:

FMCA2975

- xx

uu

Unit of Measure:

cm = Centimeters

<blank> = Inches

Length

Base Number

Example: FMCA2975-12 = 12 inches long cable
FMCA2975-100cm = 100 cm long cable

RA MMCX Plug to RA SMA Male Cable RG405 Type .086 Coax in 12 Inch from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [RA MMCX Plug to RA SMA Male Cable RG405 Type .086 Coax in 12 Inch FMCA2975-12](https://www.fairviewmicrowave.com/ra-mmcx-plug-to-ra-sma-male-cable-rg405-type-.086-coax-fmca2975-12-p.aspx)

URL: <https://www.fairviewmicrowave.com/ra-mmcx-plug-to-ra-sma-male-cable-rg405-type-.086-coax-fmca2975-12-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume liability arising out of the use of any part or document.

FMCA2975-12 CAD Drawing

RA MMCX Plug to RA SMA Male Cable RG405 Type .086 Coax in 12 Inch

